



Extract from the online catalog

SACB-C-H180-6/12- 5,0PUR SCO

Order No.: 1516616




<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1516616>

Sensor/actuator connector hood, with master cable, marking label, for an SAC box with SPEEDCON quick locking with double-occupied slots

Commercial data	
EAN	4017918967406
Pack	1 pcs.
Customs tariff	85366990
Weight/Piece	0.9854 KG
Catalog page information	Page 117 (PC-2009)

Product notes

WEEE/RoHS-compliant since:
03/29/2006



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General data	
Number of slots	6
Degree of protection	IP65/IP67/IP69K
Inflammability class acc. to UL 94	V0
Ambient temperature (operation)	-30 °C ... 80 °C
Sensor/actuator connection system	M12-SPEEDCON-socket

SACB-C-H180-6/12- 5,0PUR SCO Order No.: 1516616
<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1516616>

Master cable data

Type of connection	Pluggable screw connection
Length of cable	5 m
Cable type	Master cable suitable for flexible cable conduit
Signal line cross section	12x 0.5 mm ²
AWG signal line	20
Conductor structure, signal line	64x 0.10 mm
Power supply cross section	3x 1 mm ²
AWG power supply	17
Conductor structure, voltage supply	128x 0.10 mm
External diameter	10.5 mm
Max. bending cycles	1500000
Bending radius	110 mm
Traversing path	2 m
Traversing rate	2 m/s
Ambient temperature (operation)	-40 °C ... 90 °C (for fixed installation) -5 °C ... 80 °C (for flexible installation)
Tightening torque, cover screw	0.35 Nm
Tightening torque, union nut	2.5 Nm

Insulation material

Housing material	PBT
Material of contact, master cable side	CU alloy
Material of contact surface, master cable side	Gold-plated
Material of the contact carrier on the master cable side	PA 66 V0

Pin assignment

Slot/position = Wire color or connection	1 / 4 (A) = WH
--	----------------

SACB-C-H180-6/12- 5,0PUR SCO Order No.: 1516616
<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1516616>

	1 / 2 (B) = GY/PK
	2 / 4 (A) = GN
	2 / 2 (B) = RD/BU
	3 / 4 (A) = YE
	3 / 2 (B) = WH/GN
	4 / 4 (A) = GY
	4 / 2 (B) = BN/GN
	5 / 4 (A) = PK
	5 / 2 (B) = WH/YE
	6 / 4 (A) = RD
	6 / 2 (B) = YE/BN
	1-6 / 1 (+ 120 V) = BN
	1-6 / 3 (0 V) = BU
	1-6 / 5 (PE) = GN/YE

Certificates / Approvals



Certification

CUL, UL

SACB-C-H180-6/12- 5,0PUR SCO Order No.: 1516616
<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1516616>

Address

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 00
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2009 Phoenix Contact
Technical modifications reserved;

onlinecomponents.com