




Extract from the online catalog

## QC 1,5/15-ST

Order No.: 1718096

The figure shows a 10-position version of the product



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1718096>

Plug component, Nominal current: 12 A, Nom. voltage: 500 V, Pitch: 5 mm, Number of positions: 15, Color: green

Commercial data	
EAN	4046356140362
Pack	50 pcs.
Customs tariff	85366990
Weight/Piece	0.04077 KG
Catalog page information	Page 228 (CC-2009)

### Product notes

WEEE/RoHS-compliant since:  
05/18/2006



<http://www.download.phoenixcontact.com>  
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

## Technical data

Dimensions / positions	
Pitch	5 mm
Dimension a	70 mm
Number of positions	15

QC 1,5/15-ST Order No.: 1718096  
http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1718096

#### Technical data

Insulating material group	I
Rated surge voltage (III/3)	6 kV
Rated surge voltage (III/2)	6 kV
Rated surge voltage (II/2)	6 kV
Rated voltage (III/2)	630 V
Rated voltage (II/2)	1000 V
Connection in acc. with standard	EN-VDE
Nominal current $I_N$	12 A
Nominal voltage $U_N$	500 V
Nominal cross section	1.5 mm <sup>2</sup>
Maximum load current	12 A
Insulating material	PA
Inflammability class acc. to UL 94	V0

#### Connection data

Conductor cross section solid min.	0.2 mm <sup>2</sup>
Conductor cross section solid max.	1.5 mm <sup>2</sup>
Conductor cross section stranded min.	0.2 mm <sup>2</sup>
Conductor cross section stranded max.	1.5 mm <sup>2</sup>
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	16

#### Certificates / Approvals



Certification CUL, UL

#### CUL

Nominal voltage $U_N$	300 V
Nominal current $I_N$	10 A
AWG/kcmil	24-16

#### UL

Nominal voltage $U_N$	300 V
-----------------------	-------

QC 1,5/15-ST Order No.: 1718096

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1718096>


---

Nominal current $I_N$	10 A
AWG/kcmil	24-16

---

### Drawings

Dimensioned drawing



QC 1,5/15-ST Order No.: 1718096  
<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1718096>

---

**Address**

PHOENIX CONTACT Deutschland GmbH  
Flachmarktstr. 8  
32825 Blomberg, Germany  
Phone +49 5235 3 12000  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.de>



© 2010 Phoenix Contact  
Technical modifications reserved;

onlinecomponents.com