






⚠️ ⚠️ CABLES SOLUTIONS HIGH SPEED HDMI® CABLE WITH ETHERNET E358133 (UL) CL3 24AWG 4K x 2K CERTIFIED, ROHS COMPLIANT



PIN Assignment

P1		P2
1	Brown	1
3	White	3
2	Drain	2
4	Blue	4
6	White	6
5	Drain	5
7	Green	7
9	White	9
8	Drain	8
10	Red	10
12	White	12
11	Drain	11
13	White	13
15	Orange	15
16	Yellow	16
18		18
14	Yellow	14
19	White	19
17	Drain	17
Shell	Drain	Shell



HDI-2150	HDI-2175	HDI-2100
L=50FT±100mm	L=75FT±150mm	L=100FT±200mm

CABLE SPECIFICATION :

{[(7C/0.20TC+FPE OD:1.6mm)*1P+7C/0.20TC+Al-Foil+Mylar]*4P
 +[(7C/0.12TC+FPE OD:0.95mm)*1P+7C/0.12TC+Al-Foil+Mylar]*1F
 +(7C/0.20TC+HDPE OD:1.2mm)*1C(Red)+(7C/0.12TC+HDPE OD:0.7mm)*3C
 +Cotton+Filler+Al-Foil+1C/0.32BC+192#0.12Al-Mg+CL3 PVC OD:9.5mm}

NOTES:

- Test Condition:
 (1) 100% OPEN & SHORT TEST;
 (2) Insulation Resistance: DC300V 5MΩ(Min) ;
 (3) Conductor Resistance: 5Ω/Max.
- The product is ROHS compliant.
- HDTV-DVD TEST:1080P&3D&4K*2K
- Packaged in Quest Redmere Retail Box.

				DESCRIPTION	HDMI (M-M) Redmere HS/ENET, 4K2K, CL3, 24AWG, 2160P	SCALE	FIT	UNITS: MM	3RD ANGLE
				MODEL NO,	HDI-21xx	△			
APPROVED	CHECKED	DRAWING	DESIGNED	DRAWING NO,		△			
		ELLA	ELLA	FINISHING		△	2016/04/12		A1
				MATERIAL		SYM	DATE		REVISION