


**PIN Assignment**

P1	Color	P2	Pairing
1	Brown	1	1Pair
2	White	2	
3	Drain	3	2Pair
4	Blue	4	
5	White	5	3Pair
6	Drain	6	
7	Green	7	4Pair
8	White	8	
9	Drain	9	5Pair
10	Red	10	
11	White	11	Shell Drain Shell
12	Drain	12	
13	White	13	
14	Orange	14	
15	Yellow	15	
16	Red	16	
17	Yellow	17	
18	White	18	
19	Drain	19	



**CABLE SPECIFICATION:**  
 30AWG 1.4V HDMI Cable/OD:6.0mm/Black  
 {[(7C/0.10TC+FPE OD:0.8mm)\*1P  
 +7C/0.10TC+HDPE OD:0.5mm+MYAL]\*5P  
 +(7C/0.10TC+HDPE OD:0.55mm)\*4C  
 +AL+1C/0.254BC+128#/0.12AL+PVC OD:6.0mm}



This label to be placed on the outside of Quest cable bags

CLIENT NO:	HDI-2806	HDI-2812
LENGTH (L)	6FT±30mm	12FT±30mm

**NOTES:**

- Test Condition:
  - 100% OPEN & SHORT TEST;
  - Insulation Resistance: DC300V 5MΩ(Min) ;
  - Conductor Resistance: 5Ω/Max.
- The product is ROHS compliant.
- HDTV-DVD TEST:1080P&3D&4K\*2K

 <small>Quest Technology Int'l, Inc.          11200 NW 138th St., Medley, FL 33178          Tel: 305-513-8893 Fax: 305-513-9876          www.QuestTechnologyIntl.com</small>				DESCRIPTION	HDMI (M-M) 360DEG HS/ENET, 4K2K, PVC, 30AWG	SCALE	FIT	UNITS: MM	3RD ANGLE
APPROVED	CHECKED	DRAWING	DESIGNED	MODEL NO,	HDI-28xx	△			
				DRAWING NO,		△			
		ELLA	ELLA	FINISHING		△	2016/04/12		A1
				MATERIAL		SYM	DATE		REVISION