



REV.	Revision note	Date	Signature	Checked
1.0	PRELIMINARY	18/07/18	NDQ	






TABLE A

DRAWING NO.	Length	PART NO.
HC.HH1154.00-2081	100ft [30500±500mm]	HDI-29100
HC.HH1154.00-2082	200ft [61000±500mm]	HDI-29200
HC.HH1154.00-2083	330ft [100650±500mm]	HDI-29330
HC.HH1154.00-2084	50ft [15250±300mm]	HDI-2950
HC.HH1154.00-2085	75ft [22875±500mm]	HDI-2975

Function Test: By Player and TV test pass  
 1) Supports 4K×2K/60Hz, 4:4:4  
 2) Supports HDCP2.2  
 3) Supports ARC, HEAC  
 4) Supports 3D

NOTES:  
 1) 18.0Gbps bandwidth



NO.	PART NAME	SPEC DESCRIPTION	PART P/N	REMARK
5	Overmold	PVC+PE,Black		
4	Cover	HDMI AOC Cover,Zinc alloy,Black		
3	Conn+PCBA	HDMI A/M,PIN Gold Plated,Shell/Copper Gold Plated,with PCBA(Display)		
2	Conn+PCBA	HDMI A/M,PIN Gold Plated,Shell/Copper Gold Plated,with PCBA(Source)		
1	Cable	Optical fiber+(30AWGx1P+D+A)+26AWGx2C+28AWGx1C+30AWGx3C+F+A+PVC,OD4.5mm,Black, (TPE)		

Mould number:	Customer: Q031UU	Customer P/N: See the TABLE A	Article No./ HL-GC-001		
Packing file:	Designed by: NDQ	Checked by:	Approved by:	File number: D-2081-2085	Date: 18/07/18
				Name: HDMI(M-M) ACTIVE OPTICAL CABLE	Scale: none
			P/N: HDI-29XX	Edition: 1.0	Sheet: 1/2