


NOTE: ALL MATERIAL COMPLIANT ROHS STANDARD

REVISION INFORMATION			
Rev.	Rev. Date	Modified By	Brief Description
	2014.08.06		

" L=10FT±3.0CM"



Technical Requirements HD15P M

1.Electrical Characteristics:

1.1.cable must pass electrical testing, no short circuit, open circuit, indirect sexual contact, insufficient insulation, dislocation, and other electrical contact resistance of adverse circumstances

1.2 Electrical Test Conditions

Conductor Resistance: <10Ω
Insulation resistance: >10MΩ/300V

2.Appearance requirements:

- 2.1 No shot short.shrink. flow liner
- 2.2 Wire surface printing clear, smooth appearance, can not have scratches and obvious color
- 2.3 15PIN connector no empty pin and blunt glue
- 2.4 Terminals can not have oxidation or electrodeposited coating fall off

3.Size request

- 3.1 cable length match the drawing
- 3.2"▲" qc test according to this size



4. cable wire connect point
view the point

5.Packing:
Circle around a single package.

1).Material List :

NO.	PART NAME	SPECIFICATION DESCRIPTION	QTY	UNIT
⑦	Ferrite	Ferrite10.5*17.5*28.5mm	2	PCS
⑥	SCREW	Screw2.3*45MM	4	PCS
⑤	Outer Moalding	45P Black PVC(ROHS)	NA	KG
④	PE	PE Internal Mold Material	NA	KG
③	Connector	HD15PF Blue Bobbin Nickel-Plated	1	PCS
②	Connector	HD15PM Blue Bobbin Nickel-Plated	1	PCS
①	Wire	(7/0.12TC+1P1P6+30/0.12CCA+2.5PVC)*3Cox+7/0.12TC*8C+AL+D 7/0.12BC+1288 AL-MG OD9.5	10	FT
NO.	PART NAME	SPECIFICATION DESCRIPTION	QTY	UNIT

Wire



Packing

 Quest Technology Int'l, Inc. 11200 NW 138th St., Medley, FL 33178 Tel: 305-513-8583 Fax: 305-513-9675 www.QuestTechnologyIntl.com			
DRAWN BY	DATE: 2014/08/06	DESCRIPTION: 10FT SVGA Male to Female Cable w/Ferrite Core	
CHECKED BY	SHEET 1 of 1	ITEM NO. NCC-93XX	
APPROVED BY	SCALE 1:1	REV. 00	UNIT: mm