

SPECIFICATION CONTROL DRAWING

SCD


55A6822

Title **THREE CONDUCTOR CABLE, DOUBLE SHIELDED, DOUBLE JACKETED, GENERAL PURPOSE, 600 VOLT**

Date **2-1-18**

Revision **B**

This specification sheet forms a part of the latest issue of Raychem Specification 55A.



CABLE CONSTRUCTION DETAILS

| PART NUMBER 1/ | CONDUCTOR SIZE (AWG) | INNER SHIELD SIZE (AWG) | INNER JACKET THICKNESS (inch) | | OUTER SHIELD SIZE (AWG) | OUTER JACKET THICKNESS (inch) | | OUTSIDE DIAMETER (inch) | | MAXIMUM WEIGHT (lbs/1000 ft.) |
|-------------------|----------------------|-------------------------|-------------------------------|---------|-------------------------|-------------------------------|---------|-------------------------|---------|-------------------------------|
| | | | MINIMUM | MAXIMUM | | MINIMUM | MAXIMUM | NOMINAL | MAXIMUM | |
| 55A6822-30-* | 30 | 38 | .004 | .008 | 38 | .005 | .010 | .114 | .120 | 13.0 |
| 55A6822-28-* | 28 | 38 | .004 | .008 | 38 | .005 | .010 | .120 | .126 | 14.6 |
| 55A6822-26-* | 26 | 38 | .004 | .008 | 38 | .005 | .010 | .131 | .138 | 17.6 |
| 55A6822-24-* | 24 | 38 | .004 | .008 | 38 | .005 | .010 | .142 | .149 | 20.9 |
| 55A6822-22-* | 22 | 38 | .004 | .008 | 38 | .005 | .010 | .155 | .163 | 25.1 |
| 55A6822-20-* | 20 | 38 | .004 | .008 | 38 | .006 | .011 | .170 | .179 | 31.7 |
| 55A6822-18-* | 18 | 38 | .004 | .008 | 38 | .006 | .011 | .192 | .201 | 41.4 |
| 55A6822-16-* | 16 | 38 | .005 | .008 | 38 | .006 | .011 | .209 | .219 | 49.3 |
| 55A6822-14-* | 14 | 38 | .005 | .009 | 38 | .007 | .012 | .249 | .262 | 69.9 |
| 55A6822-12-* | 12 | 38 | .005 | .009 | 38 | .007 | .013 | .288 | .302 | 95.9 |

CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 150°C
 Maximum continuous conductor temperature
 VOLTAGE RATING: 600 volts (rms) at sea level
 BLOCKING: 200 ± 3°C for 6 hours
 CROSSLINKED VERIFICATION: 300 ± 5°C for 6 hours
 DIELECTRIC WITHSTAND:
 1500 volts (rms), 60 Hz, conductor to conductor and shield
 500 volts (rms), 60 Hz, shield to shield
 FLAMMABILITY: Procedure 1,
 3 seconds (maximum), 3 inches (maximum);
 no flaming of facial tissue
 JACKET COLOR: White preferred (each)
 JACKET ELONGATION AND TENSILE STRENGTH:
 Elongation, 50% (minimum) (each)
 Tensile Strength, 5000 lbf/in² (minimum) (each)
 JACKET FLAWS:
 Spark Test, 1.5 kV (rms)
 Impulse Dielectric Test, 6.0 kV (peak)

LOW TEMPERATURE-COLD BEND: -55 ± 5°C for 4 hours
 SHIELD COVERAGE: 85% (minimum) (each)
 VOLTAGE WITHSTAND (Post Environmental):
 1000 volts (rms), 60 Hz, 1 minute

1/ PART NUMBER:

The "*" in the part numbers above shall be replaced by color code designators with a slash separating the component wire colors, a dash separating the component wire colors from the inner jacket color, and a dash separating the inner jacket color from the outer jacket color. Colors shown do not necessarily reflect the sequence of manufacturing.
 Example: AWG 22, orange, blue, and white component wires; white inner jacket and white outer jacket:
 55A6822-22-3/6/9-9-9

This cable shall meet all constructional requirements of M27500 (AWGSB3V73).

NOTE: Nominal values are for information only. Nominal values are not requirements.

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice. TE Connectivity also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.

1/ COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681. HOWEVER, DUE TO LENGTH LIMITATIONS OF THE RAYCHEM PART NUMBER, AN ALTERNATIVE COLOR CODE MAY REPLACE MIL-STD-681 COLOR CODE DESIGNATORS. (EXAMPLE: "901/902..." MAY BE REPLACED BY "Axxx".) OTHER CODES AND SUFFIXES MAY BE ADDED TO THE PART NUMBER, AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.

