

F3-9FR Product Details



F3-9FR

TE Internal Number: C13226-001

 **Active**

Molded Parts

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Molded Part Type = Break-out
- Family Name = F
- Transition Type = Break-out
- 4 Branches/Legs
- General Purpose Application

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

 [Add to My Part List](#)  [Request Sample](#)  [Find Similar Products](#)  [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [Cable Breakout Boot, Four Entry](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Molded Part Type](#) = Break-out
- Size = 3-9
- Material = Semi rigid Modified Polyolefin

Body Related Features:

- Transition Type = Break-out
- Number of Branches/Legs = 4
- 1st Branch/Leg Range (mm [in]) = 2.79 - 7.11 [0.110 - 0.280]
- 2nd Branch/Leg Range (mm [in]) = 2.79 - 7.11 [0.110 - 0.280]
- 3rd Branch/Leg Range (mm [in]) = 2.79 - 7.11 [0.110 - 0.280]
- 4th Branch/Leg Range (mm [in]) = 2.79 - 7.11 [0.110 - 0.280]

Contact Related Features:

- Family Name = F

Housing Related Features:

- Adhesive Pre-Coating = With
- Adhesive Description = Good Water Blocking Pre-Coat Adhesive
- Max. Inside Diameter of Part (mm [in]) = 10.92 - 22.86 [0.430 - 0.900]

Configuration Related Features:

- Material Code = 3
- Adhesive Code = 97

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- Approved Standards = MIL-I-81765/1A
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- Operating Temperature (°C) = -55 - +90

Operation/Application:

- Application = General Purpose

Other:

- Brand = Raychem

 [BOOKMARK](#) 

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)


Customer Support

[Email or Chat with Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage Your Account](#)

Sign up for our eNewsletter

Enter your email address 

Follow Us On:



Visit Us On:

