



Extract from the online catalog

TT-SLKK5/110DC

Order No.: 2794932

The illustration shows version TT-SLKK5/ 12 DC



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2794932>

Modular terminal block with varistor as surge voltage protection between clamping connector and DIN rail, separate ground connection, nominal voltage: 110 V DC, mounting on NS 35/7.5, terminal width: 6.2 mm, terminal height: 69 mm

Commercial data	
EAN	4017918073008
Pack	50 pcs.
Customs tariff	85363030
Weight/Piece	0.02121 KG
Catalog page information	Page 69 (TT-2005)

Product notes

WEEE/RoHS-compliant since:
05/17/2006



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General

Housing material	PA
Inflammability class acc. to UL 94	V2
Color	black

TT-SLKK5/110DC Order No.: 2794932
http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2794932

Total surge current (8/20) μ s	6.5 kA
Ambient temperature (operation)	-40 °C ... 85 °C
Mounting type	DIN rail 35 mm
Design	Single-level terminal block – separate PE connection
Degree of protection	IP20
Direction of action	Line-Earth Ground
Width	6.20 mm
Height	69.50 mm
Length	66.50 mm
Protective circuit	
IEC category	C1
	C2
	C3
VDE requirement class	C1
	C2
	C3
Nominal voltage U_N	110 V DC
Max. operating voltage U_{max}	125 V DC
Arrester rated voltage U_C (Core-Earth)	125 V DC
Nominal current I_N	32 A (50°C)
Operating effective current I_C at U_C	$\leq 70 \mu$ A
Discharge current to PE at U_C	$\leq 70 \mu$ A
Nominal discharge surge current I_n (8/20) μ s (Core-Earth)	2 kA
Total surge current (8/20) μ s	6.5 kA
Max. discharge surge current I_{max} (8/20) μ s maximum (Core-Earth)	6.5 kA
Nominal pulse current I_{an} (10/1000) μ s (Core-Earth)	75 A
Output voltage limitation at 1 kV/ μ s (Core-Earth) spike	≤ 265 V
Output voltage limitation at 1 kV/ μ s (Core-Earth) static	≤ 240 V
Residual voltage at I_n , (conductor-ground)	≤ 390 V
Response time t_A (Core-Earth)	≤ 25 ns
Cut-off frequency f_g (3 dB), asym. (PE) in 150 Ohm system	Typ. 1 MHz

TT-SLKK5/110DC Order No.: 2794932
http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2794932

Connection data

Type of connection	Screw connection
Connection type IN	Screw terminal blocks
Connection type OUT	Screw terminal blocks
Screw thread	M3
Tightening torque, min	0.5 Nm
Stripping length	8 mm
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	4 mm ²
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12

Connection, protective circuit

Standards/regulations	IEC 61643-21
-----------------------	--------------

Certificates / Approvals



Certification CSA, CUL, GOST, UL

CSA

Nominal voltage U _N	110 V
Nominal current I _N	34 A
AWG/kcmil	28-12

CUL

Nominal voltage U _N	110 V
Nominal current I _N	30 A
AWG/kcmil	26-12


UL

Nominal voltage U _N	110 V
Nominal current I _N	30 A
AWG/kcmil	26-10

TT-SLKK5/110DC Order No.: 2794932
<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2794932>

Diagrams/Drawings

Circuit diagram



onlinecomponents.com

TT-SLKK5/110DC Order No.: 2794932
<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2794932>

Address

PHOENIX CONTACT Deutschland GmbH
Flachmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 12000
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2010 Phoenix Contact
Technical modifications reserved;

onlinecomponents.com