



# 1-1195409-6 Product Details

[Share](#) [Print](#) [Email](#)


Active

## MiniSeal Splices

D-609-08CS2603

**1-1195409-6**

TE Internal Number: 688701-000

**Product Highlights** [View All](#)

- MIL Specification [MIL-S-81824]
- Splice Type = In-Line Crimp Splice Sealing System
- Tin Wire Material
- Crimp Barrel Size = 1900 - 6755 CMA
- Not reviewed for ELV/RoHS compliance

[Pricing & Availability](#)

[Request Sample](#)

[Add to My Part List](#)

[Buy Product through Distributor](#)

Feedback

[Documents](#)

**[Features](#)**

[Compliance](#)

**Please Note:**

Use the Product Drawing for all design activity

**Product Type Features**

Splice Type	In-Line Crimp Splice Sealing System
Wire Material	Tin
Color Code	Yellow

**Termination Features**

Crimp Barrel Size (CMA [mm <sup>2</sup> ])	1900 - 6755 [0.95 - 3.37]
Connection Type	Crimp
Crimp Barrel Plating	Tin
Wire/Cable Size (AWG)	12 - 16

**Industry Standards**

Government/Industry Qualification	No
MIL Specification [MIL-S-81824]	Yes
RoHS/ELV Compliance	Not reviewed for ELV/RoHS compliance
Lead Free Solder Processes	Not relevant for lead free process

**Environmental**

Operating Temperature (Max.) (°C)	150
-----------------------------------	-----

**Operation/Application**

Application Type	Wire to Wire
------------------	--------------

**Other**

Brand	Raychem
-------	---------

**Related Products**

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

**Corporate Information**

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)
- [Global Accessibility Statement](#)

**Quick Links**

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

**Customer Support**

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

**Keep Me Informed**

