



T3-9FR Product Details

[Share](#) | [Print](#) | [Email](#)


T3-9FR

TE Internal Number: 195702-001

Active

Molded Parts

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Molded Part Type = Break-out
- Family Name = T
- Transition Type = Break-out
- 3 Branches/Legs
- General Purpose Application

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)
[Request Sample](#)
[Find Similar Products](#)
[Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [Cable Breakout Boot, Three Entry](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Molded Part Type](#) = Break-out
- Size = 3-9
- Material = Semi rigid Modified Polyolefin

Body Features:

- Transition Type = Break-out
- Number of Branches/Legs = 3
- 1st Branch/Leg Range (mm [in]) = 2.29 - 8.38 [0.090 - 0.330]
- 2nd Branch/Leg Range (mm [in]) = 2.29 - 8.38 [0.090 - 0.330]
- 3rd Branch/Leg Range (mm [in]) = 2.29 - 8.38 [0.090 - 0.330]

Contact Features:

- Family Name = T

Housing Features:

- Adhesive Pre-Coating = With
- Adhesive Description = Good Water Blocking Pre-Coat Adhesive
- Max. Inside Diameter of Part (mm [in]) = 9.14 - 22.86 [0.360 - 0.900]

Configuration Features:

- Material Code = 3
- Adhesive Code = 97

Industry Standards:

- Government/Industry Qualification = No
- Approved Standards = MIL-I-81765/1A
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Environmental:

- Operating Temperature (°C) = -55 - +90

Operation/Application:

- Application = General Purpose

Other:

- Brand = Raychem

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

