



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER	STUD SIZE	WIRE RANGE mm ² (AWG)	DIMENSIONS mm				
			A ^{±,80} (.03)	W ^{±,25} (.01)	C ^{±,38} (.01)	M ^{±,50} (.02)	H ^{±,50} (.02)
PMV6-3RB-2K	M3	4,0-6,0 (12-10)	24,9 (.98)	6,1 (.24)	7,9 (.31)	21,8 (.86)	3,3 (.13)
PMV6-35RB-2K	M3.5	4,0-6,0 (12-10)	24,9 (.98)	6,1 (.24)	7,9 (.31)	21,8 (.86)	3,7 (.15)
PMV6-4RB-2K	M4	4,0-6,0 (12-10)	25,9 (1.02)	7,9 (.31)	7,9 (.31)	21,8 (.86)	4,6 (.18)
PMV6-5RB-2K	M5	4,0-6,0 (12-10)	26,7 (1.05)	9,4 (.37)	7,9 (.31)	21,8 (.86)	5,3 (.21)
PMV6-6RB-2K	M6	4,0-6,0 (12-10)	29,2 (1.14)	10,9 (.43)	9,7 (.38)	23,9 (.94)	6,9 (.27)
PMV6-8RB-2K	M8	4,0-6,0 (12-10)	30,5 (1.20)	13,2 (.52)	9,7 (.38)	23,9 (.94)	8,6 (.34)

NOTES:

1. USED FOR:
 - A. 600V MAX. BUILDING WIRE
1000V MAX. IN SIGNS, FIXTURES, AND LUMINAIRES
 - B. 105°C (221°F) MAX. TEMP. RATING OF INSUL. MAT'L
 - C. SOLID OR STRANDED COPPER WIRE
2. PACKAGE QTY:
2K = 2000 PCS. ON CONTINUOUSLY MOLDED CARRIER STRIP
3. MATERIAL:
 - A. STAMPING: 1,02 (.04)THK. COPPER, TIN PLATED
 - B. HOUSING: YELLOW VINYL
4. WIRE STRIP LENGTH: $8,7^{+8}_{-0}$ ($11/32^{+1/32}_{-0}$)
5. DIMENSIONS IN BRACKETS ARE IN INCHES OR AWG
6. UL LISTED AND CSA CERTIFIED WITH COPPER 12-10AWG WIRE ONLY

		PANDUIT PRESS					
		CP-851 <i>DISCONTINUED</i>	CP-860 <i>DISCONTINUED</i>	CP-861	CP-862	CP-871 <i>60HZ</i>	CP-871/E <i>50HZ</i>
APPLICATORS	CA-800		X	X			
	CA-800EZ	X				X	X
	CA9				X	X	X



A41615_02

								 PANDUIT CORP. TINLEY PARK, ILLINOIS			
02	3/06	DAW	DAW	ADDED PANDUIT PRESS & APPLICATOR CHART	TR00083			2 PC. CONTINUOUSLY MOLDED VINYL INSULATED METRIC RINGS 4,0-6,0mm ² BARREL			
01	3/01	SAB	SKB	ADDED PART NUMBER PMV6-35RB-2K, ADDED CP-862, CA-9, AND CD9-3B TO NOTE 5, AND WIRE RANGE WAS 2,5-6,0	09324	JAC	TRO				
00	9/97	TM	WJB	DRAWING RELEASED	06191	LA	DBH				
REV	DATE	BY	CHK	DESCRIPTION	ECN #	CUST	PM	DRAWN BY	CHK'D	SCALE	DRAWING NO.
								T SMA	WJB	NONE	A41615