



Search by part # or keyword

[Products](#)

[Industries & Solutions](#)

[Resources](#)

[TE Store](#)

[Sign In](#)



[Harnessing](#) > [Interconnect Devices](#) > [SolderSleeve Shield Terminators](#)

# SO175-1-55-22-90

SO175-1-55-22-90



Raychem

TE Internal #: **C41212-000**

TE Internal Description: **SO175-1-55-22-90**

Alias #: **2-1200377-6**

Product Type : **Shield Terminator**

Operating Temperature (Max) (°C): **175**

Expanded Inside Diameter (Min) : **1.9 mm**

**[.075 in]**

Recovered Inside Diameter (Max) : **.5 mm [ .02 in ]**

Pre-Installed Lead : **Yes**



**ORDER SAMPLES**

[Compatible Parts & Tooling](#)

**Purchase items directly from TE.com**

### We are here to help!

Get in touch with our product experts.



**CHAT WITH US**



**EMAIL US**



**CALL US**

[Documents](#)

[Features](#)

[Product Compliance](#)

Product Drawings

SO175-1-55-22-90

[SO175-1-55-22-90](#) English

Datasheets & Catalog Pages

1654025\_Sec8\_B-155\_CWT\_SO63\_S01to03\_SO96

[ENG\\_CS\\_1654025\\_Sec8\\_B-155\\_CWT\\_SO63\\_S01to03\\_SO96\\_0313.pdf](#) English

Product Specifications

Product Specification

[ENG\\_SS\\_RT-1404\\_9.pdf](#) English

[ENG\\_SS\\_RCPS-100-70\\_K.pdf](#) English

Product Environmental Compliance

REACH Substance Communication Document

[ENG\\_PC\\_RSCD\\_HBCDD\\_1.pdf](#) English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features

Product Type : **Shield Terminator**

Configuration  
Features

Pre-Installed Lead : **Yes**

Dimensions

Jacket Outside Diameter : **1.9 mm [ .075 in ]**  
Expanded Inside Diameter (Min) : **1.9 mm [ .075 in ]**  
Recovered Inside Diameter (Max) : **.5 mm [ .02 in ]**

Usage Conditions

Operating Temperature (Max) (°C): **175**  
Resistance Properties : **Immersion Protection**  
Wire Temperature (Max) (°C): **150**



[ABOUT TE CONNECTIVITY](#)

[FOR PARTNERS](#)

[SUPPORT](#)

[CALL US](#)

[LIVE CHAT](#)

[UNITED STATES \(EN\)](#)