


204W221-25-G03/225-0



Raychem

TE Internal #: **A06542-000**

Alias #: **8-1201153-6**

Molded Part Shape : **Straight**

Molded Part Shape Code : **204**

Lipped : **Yes**

Material Code : **25**

Material Systems Code : **25**

[Similar Products](#)

Compatible Parts & Tooling

We are here to help!

Get in touch with our product experts.



CHAT WITH US



EMAIL US



CALL US

Feedback

Documents

Features

Product Compliance

Product Drawings

Dimensional Drawing

204W221-25-G03/225-0

[204W221-25-G03/225-0 \(TIFF AVAILABLE\)](#)

English

Datasheets & Catalog Pages

1654025_Sec4_-25

[ENG_CS_1654025_Sec4_-25_0313.pdf](#) English

Product Specifications

-25 MOULDED PARTS

[ENG_SS_RW-2070_2.pdf](#) English

[ENG_SS_RW-2074_2.pdf](#) English

Product Environmental Compliance

Safety Datasheet

[ENG_MSDS_RAY3111-EC-ENG_2018-08-31.pdf](#)

English

[FRE_MSDS_RAY3111-EC-FRE_2018-08-28.pdf](#)

French

Safety Datasheet

[GER_MSDS_RAY3111-EC-GER_2018-08-28.pdf](#)

German

Safety Datasheet

[ITA_MSDS_RAY3111-EC-ITA_2018-08-28.pdf](#)

Italian

Safety Datasheet

[SPA_MSDS_RAY3111-EC-SPA_2018-08-28.pdf](#)

Spanish

Safety Datasheet

[SWE_MSDS_RAY3111-EC-SWE_2018-08-28.pdf](#)

Swedish

Safety Datasheet

[DUT_MSDS_RAY3111-EC-DUT_2018-08-28.pdf](#)

Dutch

Safety Datasheet

[DAN_MSDS_RAY3111-EC-DAN_2018-08-28.pdf](#)

Danish

Safety Datasheet

[ENG_MSDS_SDS0190-EC-ENG_2014-04-10.pdf](#)

English

Safety Datasheet

[FRE_MSDS_SDS0190-EC-FRE_2014-04-10.pdf](#)

French

Safety Datasheet

[GER_MSDS_SDS0190-EC-GER_2014-04-10.pdf](#)

German

Safety Datasheet

[ITA_MSDS_SDS0190-EC-ITA_2014-04-10.pdf](#)

Italian

Safety Datasheet

[NOR_MSDS_SDS0190-EC-NOR_2014-04-10.pdf](#)

Norwegian

Safety Datasheet

[SPA_MSDS_SDS0190-EC-SPA_2014-04-10.pdf](#)

Spanish

Safety Datasheet

[SWE_MSDS_SDS0190-EC-SWE_2014-02-21_SDS190ECW.pdf](#)

Swedish

Safety Datasheet

[DUT_MSDS_SDS0190-EC-DUT_2014-04-10.pdf](#)

Dutch

Safety Datasheet

[DAN_MSDS_SDS0190-EC-DAN_2014-04-10.pdf](#)

Danish

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features

Molded Part Shape : **Straight**

Configuration Features

Lipped : **Yes**

Body Features

Material Code : **25**

Material Systems Code : **25**

Adhesive Pre-Coat : **Yes**

Material : **Fluid Resistant Modified Elastomer**

Dimensions

Inside Diameter as Supplied : **11 mm [.43 in]**

Usage Conditions

Operating Temperature Range : **-75 – 150 °C [-103 – 302 °F]**

Operation/Application Power Cable Accessory : **No**

Industry Standards

Approved Standards : **VG95343 Parts 6,7,8 and 9**
Government Qualified : **No**

Other

Molded Part Shape Code : **204**
Fluid/Chemical Resistance :
Long-Term Exposure at High Temperature

EU RoHS Directive 2011/65/EU

EU RoHS Directive with Phthalates Amendment 2011/65/EU, 2015/863/EU

The 4 Phthalates substances of amendment 2015/863/EU only become restricted as of 22 July 2019 for all electrical and electronic equipment, apart from Categories 8 (medical devices) and 9 (monitoring and control equipment) for which the restriction applies as of 22 July 2021.

EU ELV Directive 2000/53/EC

China RoHS 2 Directive MIIT Order No 32, 2016

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: **JAN 2019 (197)**
Candidate List Declared Against: **JUN 2018 (191)**

Halogen Content

Solder Process Capability

Not applicable for solder process capability

Statement of Compliance

[Statement of Compliance pdf](#)

Compliance Documents

There may be Environmental Compliance related documents on the [DOCUMENTATION Tab](#)

Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The

part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Products with Similar Specs

[View All Similar Products](#)

THIS PRODUCT

TOP RESULTS ?


HEAT SHRINK BOOTS
204W221-25-G03/225-0



Non-Stocked

Molded Part Shape : Straight
Molded Part Shape Code : 204
Lipped : Yes
Material Code : 25
Material Systems Code : 25


HEAT SHRINK BOOTS
224W201-25/225-0



Non-Stocked

Molded Part Shape : 90°
Molded Part Shape Code : 224
Lipped : Yes
Material Code : 25
Material Systems Code : 25


HEAT SHRINK BOOTS
224W221-25/225-0



Non-Stocked

Molded Part Shape : 90°
Molded Part Shape Code : 224
Lipped : Yes
Material Code : 25
Material Systems Code : 25

HEAT SHRINK BOOTS
204W221-25/225-0



Non-Stocked

Molded Part Shape : Straight
Molded Part Shape Code : 204
Lipped : Yes
Material Code : 25
Material Systems Code : 25

