



**HARNESSING**

**HEAT SHRINK BOOTS**



✓ Active

TE CONNECTIVITY (TE)

**222D211-4/86-0**

Raychem | CAP , CRPS

222D211-4/86-0

TE Internal Number: 492575-000

Alias ID: 2-1193684-8

EU RoHS Compliant

EU ELV Compliant

Lipped Yes

Operating Temperature Range (°C) -55 – 105

Fluid/Chemical Resistance Suitable for occasional exposure to fluids

Adhesive Options /86 Precoat, -55 – 105°C (-67 – 221°F)

Material Systems Code 10

[↓ PRODUCT DRAWING](#)  
English

## DOCUMENTATION

Product Drawings

**Boot, 90 Deg., With Lip**

PDF

English

Product Specifications

Product Specification

**Thermofit Polyolefin Molded Components Flame-Retarded, Flexible, Heat-Shrinkable**

PDF

English

Product Environmental Compliance

Safety Data Sheet

**Aliphatic Polyamide Based Adhesives.**

PDF

**Dutch**

**Aliphatic Polyamide Based Adhesives.**

PDF

**English**

**Aliphatic Polyamide Based Adhesives.**

PDF

**French**

**Aliphatic Polyamide Based Adhesives.**

PDF

**German**

**Aliphatic Polyamide Based Adhesives.**

PDF

**Italian**

**Aliphatic Polyamide Based Adhesives.**

PDF

**Spanish**

**Aliphatic Polyamide Based Adhesives.**

PDF

**Swedish**

**EPS Heat Shrinkable Polymeric Products**

PDF

**English**

**EPS Heat Shrinkable Polymeric Products**

PDF

**French**

**EPS Heat Shrinkable Polymeric Products**

PDF

**German**

**EPS Heat Shrinkable Polymeric Products**

PDF

**Italian**

**EPS Heat Shrinkable Polymeric Products**

PDF

**Norwegian**

**EPS Heat Shrinkable Polymeric Products**

PDF

**Spanish**

**EPS Heat Shrinkable Polymeric Products**

PDF

**Swedish**

**EPS Heat Shrinkable Polymeric Products**

PDF

**Dutch**

**EPS Heat Shrinkable Polymeric Products**

PDF

Danish

## Aliphatic Polyamide Based Adhesives.

PDF

English

### FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

#### Product Type Features

**Molded Part Type** Molded Boot

#### Configuration Features

**Lipped** Yes

#### Body Features

**Material Systems Code** 10

**Adhesive Pre-Coat** Yes

**Entry Size (Braided or Magneform Adapter)** 5, 6

**Entry Size (Spin Coupling Adapter)** 4 – 5

**Entry Size (Tinel-Lock Adapter)** 4, 5

**Material** Modified Polyolefin

#### Dimensions

**Cable Diameter Range** 6.4 – 14 mm [ .252 – .551 in ]

**Wire/Cable Outside Diameter** .276 in, .3 in, .31 in, .35 in, .39 in, .43 in, .433 in, .47 in, 10 mm, 11 mm, 12 mm, 7 mm, 8 mm, 9 mm

#### Usage Conditions

**Operating Temperature Range (°C)** -55 – 105

#### Operation/Application

**Power Cable Accessory** No

#### Industry Standards

**Government Qualified** No

**Approved Standards** SAE AS I 81765/1, Type II, UL 224, File E85381

#### Other

**Fluid/Chemical Resistance** Suitable for occasional exposure to fluids

**Adhesive Options** /86 Precoat, -55 – 105°C (-67 – 221°F)

**Adhesive Type** High Performance Pre-Coat Adhesive

### PRODUCT COMPLIANCE



Statement of Compliance

**Statement of Compliance**

PDF

---