

Search Results

- Evaluate
 - FAQ's
- Design a Solution
 - Catalog Cut Sheet
 - PDFDNG18250FL- ..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips

 Text Search: 'DNF10250FIBG2K'

Your search criteria matched only one product, shown below

DNF10250FIBG2K



- Continuously molded design provides reliable, consistent performance through the applicator for a high quality termination every time
 - Disconnect can be inserted and removed from the male tab without the use of tools for lower installed cost
 - Fully insulated design provides protection from electrical shorts
 - Disconnects available in common industry tab sizes
 - Internal wire stop assures proper length of insertion into terminal barrel, providing a higher quality connection
 - UL Flammability UL 94V -2/HB, maximum insulation temperature 221°F (105°C)
 - UL and CSA rated up to 600 V per UL 310, where applicable
- Refer to customer drawings on Panduit website for technical specifications

Part Number	DNF10250FIBG2K
RoHS Compliancy Status	Compliant
Part Description	Disconnect, compressor tab, nylon, fully insulated, #12– 10 AWG, .250 X .032 tab.
Height (In.)	0.23
Height (mm)	5.8
Length (In.)	0.96
Length (mm)	24.4
Width (In.)	0.35
Width (mm)	8.9
CA-800/EZ Series Crimp Die	CD-800-13
CA9 Series Crimp Die	CD9-13B
CE Compliant	No
Insulation	Nylon
Max. Ins.	0.220
Max. Ins. (mm)	5.6
Panduit Color Code	Yellow
Pieces Per Reel	2000
Plating Type	Tinned
Pricing Description	Female Disconnect, compressor tab, nyl fully insul, 12- 10 AWG, .250 x .032 tab
Tab Size (In.)	0.250 x 0.032
Tab Size (mm)	6.4 x 0.8
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)
Wire Range	12 – 10 AWG
Wire Range (mm ²)	2.5 – 6.0
Min. Order UOM	PC
Min. Order Qty.	2000
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.