

- FAQ's
- Design a Solution
 - Part Drawings
 - PDF Fiber Optic..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Current refinements (click to remove) Search Tips

Text Search: 'F6LD3-3M7'

F6LD3-3M7



- Pass all TIA/EIA-568-B.3 performance requirements
- Insertion loss per connection: 0.10dB typical; 0.30dB maximum
- Factory terminated and 100% tested for insertion loss
- Insertion loss data recorded for every multimode patch cord
- Lifetime traceability of test data to a Q.C. number on each patch cord
- SC Duplex Patch Cords include SC Duplex Clips to maintain polarity
- Highest quality flame retardant fiber optic cable with tight -buffered coating on each optical fiber

Additional lengths and availability: Patch cords are available in 1 – 10 meter lengths in 1 meter increments, and 15, 20, 25 and 30 meter lengths. Pigtails are available in 1, 2, and 3 meter lengths. Ex: To order lengths other than 1 meter, replace the 1 after the M (F6D2 -2M1Y) with the desired length (FF6D2 -2M2Y for 2 meter length). The above lengths are stock items. For other lengths, contact Customer Service for actual lead times.

Part Number	F6LD3-3M7
RoHS Compliancy Status	RoHS directive is not applicable
Note	Intended for use in fixed installations which are outside the scope of RoHS
Part Description	SC to SC multimode duplex patch cord, 3mm jacketed cable (one duplex SC connector on each end) – 62.5/125µm.
Product Type	SC Patch Cords
Length (m)	7
Fiber Compatibility	62.5/125µm
Fiber Cable Size	3mm
Fiber Cable Type	Jacketed
Fiber Type	Multimode
Cable Color	Orange
Cable Type	Duplex
CE Compliant	No
Connector 1 Type	SC Connector
Connector 2 Type	SC Connector
End Configurations	SC to SC
Fiber Count	2
Flammability Rating	Low Smoke Zero Halogen (LSZH)
Pricing Description	SC-SC 62.5µm LSZH Dupl PC 3mm 7m
Min. Order UOM	PC
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	e

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.