



## HEAT SHRINK TUBING



✓ Active

TE CONNECTIVITY (TE)

### RNF-3000-12/4-1-SP

Raychem | RNF-3000

RNF-3000-12/4-1-SP

TE Internal Number: 0546234002

Alias ID: 7-1190416-6

EU RoHS Compliant

EU ELV Compliant

Wall Type Single

Resistant To Abrasion, Fluids, Mechanical Damage, Strain

Low Outgassing No

Product Source Czech Republic

Packaging Method Spool

## DOCUMENTATION

Catalog Pages/Data Sheets

**RNF-3000 Pages From 9-1773447-9**

PDF

English

Product Specifications

Product Specification

**RNF-3000 Sleeving**

PDF

English

Product Environmental Compliance

Safety Data Sheet

**Thermofit Heat-Shrinkable Polymeric Products**

PDF

English

## Thermofit Heat-Shrinkable Polymeric Products

PDF

**Danish**

## Thermofit Heat-Shrinkable Polymeric Products

PDF

**Dutch**

## Thermofit Heat-Shrinkable Polymeric Products

PDF

**English**

## Thermofit Heat-Shrinkable Polymeric Products

PDF

**French**

## Thermofit Heat-Shrinkable Polymeric Products

PDF

**German**

## Thermofit Heat-Shrinkable Polymeric Products

PDF

**Italian**

## Thermofit Heat-Shrinkable Polymeric Products

PDF

**Norwegian**

## Thermofit Heat-Shrinkable Polymeric Products

PDF

**Spanish**

## Thermofit Heat-Shrinkable Polymeric Products

PDF

**Swedish**

## Thermofit Heat-Shrinkable Polymeric Products

PDF

**Spanish**

## Thermofit Heat-Shrinkable Polymeric Products

PDF

**English**

## Thermofit Heat-Shrinkable Polymeric Products

PDF

**English**

## FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

---

Product Type Features

**Wall Type** Single

**Product Family** RNF-3000

---

## Electrical Characteristics

**Voltage (Max) (kV)** .6

---

## Body Features

**Shrink Ratio** 3:1

**Color** Brown

**Flexibility** Flexible

**Fluid Type** Gasoline, Hydraulic Fluid, Lubricating Oil

**Material** Irradiated Modified Polyolefin

---

## Dimensions

**Expanded Inside Diameter (Min)** 12 mm [ .472 in ]

**Recovered Inside Diameter (Max)** 4 mm [ .157 in ]

**Recovered Wall Thickness (Tolerance)** .75 mm [ .005 in ]

**Recovered Wall Thickness (Nominal)** .75 mm [ .03 in ]

---

## Usage Conditions

**Resistant To** Abrasion, Fluids, Mechanical Damage, Strain

**Recovery Temperature (°C)** 120

**Operating Temperature Range (°C)** -55 – 135

**Flammability** Flame-Retardant

**Shrink Temperature (Min) (°C)** 80

**Fluid Resistance** Splash Protection

---

## Product Availability

**Applicable Region** Global

---

## Packaging Features

**Packaging Method** Spool

---

## Other

**Low Outgassing** No

**Product Source** Czech Republic

---

## Statement of Compliance

**Statement of Compliance**

PDF