

Products

- Products Overview
- Product Search**
- Evaluate
 - FAQ's
- Design a Solution
 - Catalog Cut Sheet
 - PDFLCCX8-10A-L
 - PDFLCCX8-14A-L
 - Part Drawings
 - PDF Copper, Long..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Product Search >

Current refinements (click  to remove) Search Tips

Part Description > Flex lug, long barrel, 650 kcmil, 2hole, 1/2" stud holes, 1.75 hole spacing.

Your search criteria matched only one product, shown below

LCCX650-12-6



For Use with Flexible, Extra-Flexible, and Code Stranded Copper Conductors

- Can be used with code conductor and flex conductor class: G, H, I, K, M and Diesel Locomotive
- Long barrel maximizes number of crimps and provides premium wire pull -out strength and electrical performance
- Generously beveled wire entry prevents bent back strands when inserting conductor into barrel
- Color-coded barrels marked with Panduit and specified competitor die index numbers for proper crimp die selection
- Inspection window to visually assure full conductor insertion
- Tin-plated to inhibit corrosion
- UL Listed and CSA Certified to 35 KV** and temperature rated to 90°C when crimped with Panduit and specified competitor crimping tools and dies
- Meets J-STD-607-A and TIA-942 requirements for network systems grounding applications
- Available with NEMA hole sizes and spacing

Note: These flex conductor lugs are manufactured for use with AWG wire only.

Part Number	LCCX650-12-6
RoHS Compliancy Status	Compliant
Part Description	Flex lug, long barrel, 650 kcmil, 2hole, 1/2" stud holes, 1.75 hole spacing.
Material	Tin-Plated Copper
CSA Certified	Yes
UL Listed	Yes
Length (In.)	6.75
Length (mm)	171.5
Diesel Locomotive	646.4 kcmil
Stud Hole Size (In.)	1/2
Stud Hole Spacing (In.)	1.75
Tongue Width (In.)	1.95
Barrel Length (In.)	2.94
Angle	Straight
Barrel Length (mm)	74.7
CE Compliant	No
Figure No.	1
Panduit Color Code	Black
PANDUIT Die Color & Die No.	Black P106
Panduit Die Index No.	P106
Pattern	N
Pricing Description	Copper Comp. Lug, 2 Hole, 650 kcmil Flex, 1/2" (12.7mm) Stud, 1.75" (44.4mm) Hole Sp.
Stud Hole Size (mm)	12.7
Tongue Thickness	0.30
Tongue Type	Standard
Tongue Width (mm)	49.5
Tool	CT-930, CT-2930/L, CT-2930/LE
Wire Strip Length (In.)	3.00
Wire Strip Length (mm)	76.2
Min. Order UOM	PC
Min. Order Qty.	1
Burndy Die Index No.	24
T&B Die Index No.	106H
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.