

Search Results

- Evaluate
 - FAQ's
- Design a Solution
 - Part Drawings
 - PDFContour Ty C ..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips  Within Results

 Text Search: 'CBR3S-M30'

Your search criteria matched only one product, shown below

CBR3S-M30



- For high temperature applications up to 239°F (115°C) – indoor use
- Unique design prevents wire and cable damage
- Low profile head avoids snags and reduces overall bundle size
- Outside teeth and smooth round edges protect cable jacket – ideal for high vibration applications
- Parallel-entry limits exposure to sharp edges and protects workers' arms and hands
- Fully enclosed head for consistent strength
- Curved tip is easy to pick up from flat surfaces and allows faster initial threading to speed installation

Part Number	CBR3SM30
RoHS Compliance Status	Compliant
Part Description	Contour-Ty® Cable Tie, Parallel-entry, 10.8", Standard cross section
Product Type	Cable Ties
Material	Heat Stabilized Nylon 6.6
Color	Black
CSA Certified	Yes
UL Listed (File #E56854)	Yes
UL Recognized (File #E56854)	Yes
Length (In.)	10.8
Length (mm)	274
Width (In.)	.190
Width (mm)	4.8
CE Compliant	Yes
Cross Section	Standard
Head Height (In.)	.215
Head Height (mm)	5.5
Head Width (In.)	.332
Head Width (mm)	8.4
Locking Style	Locking
Material Flammability Rating	UL 94V-2
Max. Bundle Diameter (In.)	3.00
Max. Bundle Diameter (mm)	76
Max. Continuous Use Temperature	239°F (115°C)
Min. Loop Tensile Strength (Lbs.)	50
Min. Loop Tensile Strength (N)	222
Pricing Description	Cable Tie, InLine, 10.8"L (274mm), Standard, Heat Stabilized, Black
Thickness (In.)	.052
Thickness (mm)	1.3
Tool	GTS, GTSL, GS2B, GTH, GS4H, PTS, PTH, PPTS, STS2, STH2
Min. Order UOM	PC
Min. Order Qty.	1000
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.