



Search Results

- Evaluate
- FAQ's
- How to Buy
- Bill of Material
- Favorite Products List
- Locate Distributor

[Home](#) > [Products Overview](#) > [Search Results](#) >

Current refinements (click to remove) [Search Tips](#) Within Results

Text Search: 'HSECFR0.8X'

Your search criteria matched only one product, shown below

HSECFR0.8-X



- Heat indicating line ensures correct temperature is applied
 - Cross -linked, UV resistant material improves flame retardancy, chemical, and temperature resistance
 - Shrink ratio of 3:1 insulates a wide range of diameters and irregular shapes, which reduces inventory costs
- * Flame retardant products are manufactured from a material that is rated UL94V -0.

	Part Number	HSECFR0.8X
	RoHS Compliancy Status	If RoHS Decabrome Free Part required use HSECFR0.8Y
	Note	Call Customer Service for Pricing, Availability, etc.
	Part Description	Flame Retardant Thick Wall End Caps
	Material	Flame retardant cross-linked polyolefin with adhesive
	Color	Black
	Copper Conductor Size Range	#6 – #2 AWG
	Cap Length (In.)	3.50
	Cap Length (mm)	88.9
	Conductor Size Range (mm ²)	25 to 95
	Max. Recovered I.D. (In.)	.24
	Max. Recovered I.D. (mm)	6.1
	Min. Expanded I.D. (In.)	.75
	Min. Expanded I.D. (mm)	19.0
	Nominal Recovered Wall Thickness (In.)	.090
	Nominal Recovered Wall Thickness (mm)	2.4
	Pricing Description	Heat Shrink Thick Adhesive End Cap, .8"(20mm)
	Temperature Range	-67°F to 230°F (-55°C to 110°C)
	Min. Order UOM	PC
	Min. Order Qty.	10
	BOM Qty. (# of Pkgs.)	0
	Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.