

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	W	PRODUCTION ISSUE	18JAN2019	PNT	MT





TABLE OF DIMENSIONS


PART NUMBER	H		P	W
	Min a	Max b	Min b	$\pm 20\%$ b
101A011	5.1 [.20]	2.0 [.08]	22.9 [.90]	1.02 [.04]
101A021	7.4 [.29]	3.3 [.13]	25.4 [1.00]	1.27 [.05]
101A031	10.2 [.40]	4.6 [.18]	30.5 [1.20]	1.52 [.06]
101A041	15.2 [.60]	6.4 [.25]	40.6 [1.60]	1.78 [.07]
101A052	20.6 [.81]	9.4 [.37]	61.0 [2.40]	2.03 [.08]
101A062	25.4 [1.00]	11.4 [.45]	68.6 [2.70]	2.29 [.09]
101A073	39.4 [1.55]	18.0 [.71]	91.4 [3.60]	2.54 [.10]
101A083	50.8 [2.00]	22.9 [.90]	101.6 [4.00]	2.79 [.11]
101A094	83.8 [3.30]	38.1 [1.50]	114.3 [4.50]	3.05 [.12]

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

COPYRIGHT - TE Connectivity Ltd.

DIMENSIONS: mm [INCHES]	DWN PRAVEEN N T	18JAN2019	MATERIAL SEE SHEET 2	FINISH -
	CHK N NAGAR	18JAN2019	 TE Connectivity Ltd.	
TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD M TAYLOR	18JAN2019		
	PRODUCT SPEC -	SIZE A4		CAGE CODE 00779
0 PLC $\pm -$	APPLICATION SPEC -	RESTRICTED TO -		WEIGHT
1 PLC ± 0.50 [.10]		SCALE DNS		SHEET 1 OF 2
2 PLC ± 0.25 [.01]		REV W		
3 PLC ± 0.13 [.005]	CUSTOMER DRAWING			
4 PLC $\pm -$				
ANGLES $\pm 1^\circ$				

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

COMPATIBILITY CHART

MATERIAL DASH NO.	MATERIAL DESCRIPTION	RT SPEC	COATING SLASH NO.	COATING S NO.
—3	Polyolefin, Semi-rigid	RT-301	/42;/86;/180	S1017;S1048;S1030
—4	Polyolefin, Flexible	RT-1304	/42;/86;/180	S1017;S1048;S1030
—12	Fluoroelastomer, Flexible	RT-1312	N/A	N/A
—25	Elastomer, Fluid Resistant	RW-2070	/42;/86;/225	S1017;S1048;S1206
—100	Polyolefin, Semi-flexible Zerohal	RW-2082	/86;/180	S1048;S1030

ORDERING INFORMATION

	101A021	—XX	—XX	/XX	—0
Base part number					
Material dash number (See Compatibility Chart)					
Modification number					
Adhesive slash number (If necessary, see Compatibility Chart)					
Color designator					

NOTES

- Dimensions appearing in table are as follows:
 - As Supplied
 - After Unrestricted Recovery
- Coating is optional. As supplied dimensions appearing in table are for uncoated parts. When coating is added, entry diameters will be reduced by 1.5mm[.06] max.
- Recovered parts may have angularity of 30° – 45°.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

TE Connectivity Ltd.

COPYRIGHT

DIMENSIONS:
mm [INCHES]

DWN 18JAN2019
PRAVEEN N T

CHK 18JAN2019
N NAGAR

APVD 18JAN2019
M TAYLOR

MATERIAL

—

FINISH

—

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± —

1 PLC ± 0,50 [.10]

2 PLC ± 0,25 [.01]

3 PLC ± 0,13 [.005]

4 PLC ± —

ANGLES ± 1°

PRODUCT SPEC

—

APPLICATION SPEC

—

WEIGHT

NAME

CAP, ROUND END

SIZE

A4

CAGE CODE

00779

DRAWING NO

C- 101A011-XX-0THRU094-XX-0

RESTRICTED TO

—

CUSTOMER DRAWING

SCALE

DNS

SHEET

2 OF 2

REV

W

