

Search Results

- Evaluate
 - FAQ's
- Design a Solution
 - Part Drawings
 - PDF Copper, Long ..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click to remove) Search Tips Within Results

Code Conductor, Two -Hole, Long Barrel Lug, 90° Angle > Text Search: 'LCC4/0-12F-X'

LCC4/0-12F-X



For Use with Stranded Copper Conductors

- Long barrel maximizes number of crimps and provides premium wire pull -out strength and electrical performance
- Color-coded barrels marked with *PANDUIT* and specified competitor die index numbers for proper crimp die selection
- Enclosed barrel prevents corrosive material from entering barrel when used in harsh environments
- Tin-plated to inhibit corrosion
- UL Listed and CSA Certified to 35 KV** and temperature rated to 90°C when crimped with *PANDUIT* and specified competitor crimping tools and dies
- UL Listed and CSA Certified for wide wire range -taking

capability when crimped with *PANDUIT*® *Uni-Die*™ Dieless Crimping Tools†

- **Tested by Telcordia – meets NEBS Level 3**
- American Bureau of Shipping Approved
- Available with NEMA hole sizes and spacing

Part Number	LCC4/0-12F-X
RoHS Compliancy Status	Compliant
Part Description	Two-hole, long barrel lug, 4/0 AWG wire, 1/2" stud hole, 1 3/4" hole spacing, 90° angle tongue.
CSA Certified	Yes
UL Listed	Yes
Length (In.)	3.98
Length (mm)	101.1
Copper Conductor Size	4/0 AWG
Stud Hole Size (In.)	1/2
Stud Hole Spacing (In.)	1.75
Tongue Width (In.)	1.06
Barrel Length (In.)	1.56
Angle	90°
Clearance	.63
Panduit Color Code	Purple
Panduit Die Index No.	P54
Pricing Description	Copper Compression Lug, 2 Hole, 4/0 AWG, 1/2" (12.7mm) Stud, 90° Bent
Stud Hole Size (mm)	M12
Tongue Thickness	.14
Tongue Type	Standard
Tongue Width (mm)	26.9
Wire Strip Length (In.)	1 5/8
Min. Order UOM	PC
Min. Order Qty.	1
Burndy Die Index No.	15
T&B Die Index No.	54
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Related Products

- [Contour Crimp™ Co ..](#)
- [Die Type, Manual, Crimping Too ..](#)
- [CD-720 Crimping Dies](#)
- [Die Type, Manual Hydraulic, 14 ..](#)
- [Die Type, Remote Hydraulic, 14 ..](#)
- [More...](#)

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.