

Search Results

- Evaluate
 - FAQ's
- Design a Solution
 - Part Drawings
 - PDFMLT, SuperH ..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips  Within Results

 Text Search: 'MLT12SH-Q316'

Your search criteria matched only one product, shown below

MLT12SH-Q316




The *Pan-Steel*[®] system provides a strong durable method of bundling and fastening. Stainless steel cable ties can be used in virtually all indoor, outdoor and underground (including direct burial) applications. They are especially well suited for network bundling of data and power cables. Their high strength, non-flammability, fully rounded edges and exclusive easy thread lead-in design provide the ultimate support for network cables.

- Self-locking head design speeds installation and locks into place at any length along the tie body
- Provides a strong, durable method of cable bundling
- Can be used in a wide range of indoor, outdoor, and underground (including direct burial) applications
- Smooth surfaces and rounded edges assures cable protection and worker safety
- Available in AISI 304 stainless steel for general -purpose applications
- Available in AISI 316 stainless steel for the most corrosive environments

Product Specifications

- Material: Type 304 or 316 stainless steel
- Temperature range: -112°F (-80°C) to 1000°F (538°C)
- Water absorption: none
- Flammability: non-flammable
- Ultraviolet resistance: excellent
- Chemical resistance: excellent
- Radiation resistance: 2 x 10⁸ rads
- Loop tensile strength range: 200 -900 lbs. (890 -4005N) (see chart for sizes)
- Fully rounded edges and smooth surfaces
- Estimated outdoor service life of 40 years

Part Number	MLT12SHQ316
RoHS Compliancy Status	Compliant
Part Description	Stainless steel cable tie, super-heavy, 12" (305mm) max bundle diameter.
Product Type	Cable Ties
Material	Stainless Steel Type 316
Length (In.)	42.2
Length (mm)	1072
Width (In.)	.63
Width (mm)	16.0
Cross Section	Super-Heavy
Max. Bundle Diameter (In.)	12.0
Max. Bundle Diameter (mm)	305
Min. Bundle Diameter (In.)	1.00
Min. Bundle Diameter (mm)	25.4
Min. Loop Tensile Strength (Lbs.)	900
Min. Loop Tensile Strength (N)	4005
Pricing Description	MLT Tie, 316 SS, Super Heavy, 42.2" (1072mm), .015" (.38mm) thk
Thickness (In.)	.015
Thickness (mm)	.38
Tool	RT1HT, RT1HTN
Min. Order UOM	PC
Min. Order Qty.	25
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.