

Current refinements (click to remove)

Search Tips

Region **USA** Product Family **Braided Expandable Sleeving – Flame Retardant Polyethylene Terephthalate**
 Text Search: 'SE50PFR-DR10'

Your search criteria matched only one product, shown below.



- Provides continuous abrasion resistance for wires cables and tubing
- Lightweight durable protection
- Highly flexible open weave will not trap heat or humidity
- Rated for use up to 257°F (125°C)
- Allows for use with irregular shapes
- Self extinguishing meets UL VW-1
- Stock colors: Black or gray with white tracer or in white with black tracer to identify flame retardant materials.

Part Number:	SE50PFRDR10
RoHS Compliancy Status:	Compliant
Part Description:	Flame Retardant Braided Expandable Sleeving provides continuous abrasion resistance for wires, cables and tubing. The highly flexible open weave will not trap heat or humidity.
Material:	Flame Retardant Polyethylene Terephthalate
Color:	White
CSA Certified:	Yes
UL Recognized:	E116868
Flammability Rating:	UL224 VW-1
Length Per Reel (ft.):	500
Length Per Reel (m):	152.4
Nominal Diameter Range (In.):	.250 to .750
Nominal Diameter Range (mm)	6.4 to 19.1
Nominal I.D. (In.):	.50
Nominal I.D. (mm):	12.7
Temperature Range:	-94°F to 257°F (-70°C to 125°C)
Min. Order UOM:	RL
Min. Order Qty.:	1
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to My Catalog	<input type="checkbox"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'My Catalog' features.