




Wire & Cable > High Speed Digital & Data Cable



Cable Type: **Coaxial**

Impedance: **50 Ω**

Wire Size: **20 AWG**

Operating Temperature Range: **-55 – 115 °C [-67 – 239 °F]**

Features

Product Type Features

Cable Style	Round Braided
-------------	---------------

Electrical Characteristics

Capacitance	.0000264 pF/m[26.4 pF/ft]
Impedance	50 Ω

Signal Characteristics

Velocity of Propagation	77 %
-------------------------	------

Body Features

Jacket Material	Thermorad S
Shield Type	Single
Conductor Material	Tin-Plated Copper
Cable Color	Black
Shield Plating Material	Tin
Shield Material	Copper

Dimensions

Conductor Diameter Range	1.02 mm[.04 in]
Outside Cable Diameter	3.76 mm[.148 in]
Cable Dielectric Diameter	2.72 mm[.107 in]
Wire Size	20 AWG



Usage Conditions

Cable Type	Coaxial
Operating Temperature Range	-55 – 115 °C[-67 – 239 °F]

Other

Dielectric Material	Rayfoam L
Product Source	US

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #EJ1976-000
06171401



TE Part #5069914004
CGPT-1.2/0.6-9-SP



TE Part #747521-2
HDP-20,OVRLD RCPT SUBASSY,SIZ



TE Part #1411576-1
ELO 0.63, CONTACT



TE Part #1623925-3
CFR100 5% 10K



TE Part #2176416-8
9W STD M/OX 5% 100R




TE Part #7-2176614-3
EP 10W (SS) 1K0 5% BULK BOX



TE Part #5413631-1
JACK,RTANG, PCB,50 OHM, BNC



TE Part #5535090-4
ASSEMBLY,RECEPTACLE,EUROCARD, T



TE Part #5650947-5
ASSY,PIN,EUROCARD,TYPE C,LEAD-

Documents

Product Drawings
5020A1311-0

English

Datasheets & Catalog Pages
Raychem Cheminax RF Coaxial Cables and RF Connectors Selection Guide

English

Product Specifications
Product Specification

English