


[support](#) | [locate distributor](#) | [about panduit](#) | [careers](#) | [worldwide](#)
World Leader in Network and Electrical Solutions
[Printer Friendly](#)
[HOME](#) | [SOLUTIONS](#) | [RESOURCES](#) | [PRODUCTS](#) | [SERVICES](#) | [LEARNING](#)

SEARCH


 Current refinements (click to remove)

[Search Tips](#)
 [Region](#) ▶ [USA](#)
 [Product Family](#) ▶ [Braided Expandable Sleeving – Polyethylene Terephthalate \(PET\)](#)
 [Text Search: 'SE125P-TR10'](#)
Your search criteria matched only one product, shown below.


- Provides continuous abrasion resistance for wires cables and tubing
- Lightweight durable protection
- Highly flexible open weave will not trap heat or humidity
- Rated for use up to 257°F (125°C)
- Allows for use with irregular shapes
- Stock colors: Black gray and white

Part Number:	SE125P-TR10
RoHS Compliancy Status:	Compliant
Part Description:	Braided Expandable Sleeving provides continuous abrasion resistance for wires, cables and tubing. The highly flexible open weave will not trap heat or humidity.
Material:	Polyethylene Terephthalate
Color:	White
CSA Certified:	Yes
UL Recognized:	E116868
Length (ft.):	200
Length (m):	61.0
Flammability Rating:	UL94 HB
Nominal Diameter Range (In.):	.750 to 1.50
Nominal Diameter Range (mm):	19.1 to 38.1
Nominal I.D. (In.):	1.25
Nominal I.D. (mm):	31.8
Temperature Range:	-94°F to 257°F (-70°C to 125°C)
Min. Order UOM:	RL
Min. Order Qty.:	1
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to My Catalog	<input type="checkbox"/>

 Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'My Catalog' features.

[legal information](#) | [privacy policy](#) | [site map](#)

Copyright © 1995-2007, PANDUIT CORP. All rights reserved.