B-801-36 ✔ ACTIVE

RAYCHEM

TE Internal #: 695463-000

22 – 26 AWG, .34 – .14 mm² Wire, Fully Insulated, 9 mm [.354 in] Length, Bag, Stranded Wire, Discrete Wire, -55 – 150 °C [-67 – 302 °F]

View on TE.com >

Terminals & Splices > Splices



Wire Size: **.34 – .14 mm²**

Sealable: **No**

Compatible Insulation Diameter Range: **1.4 mm [.055 in]**

Product Length: **9 mm [.354 in]**

Features

Product Type Features

Sealable	No
Compatible With Discrete Wire Type	Stranded

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire

Body Features

Insulation Material	Heat Shrink Radiation-Crosslinked Modified Polyvinylidene

Termination Features

Termination Method to Wire & Cable	Solder

Housing Features

Housing Material	Polyvinylidene

Dimensions

Recovered Inside Diameter	1.4 mm[.055 in]
Wire Size	.34 – .14 mm²
Compatible Insulation Diameter Range	1.4 mm[.055 in]
Product Length	9 mm[.354 in]

Usage Conditions

Insulation Option	Fully Insulated

Operating Temperature Range	-55 – 150 °C[-67 – 302 °F]

Industry Standards

Government Qualified Splice	No

Packaging Features

Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量超出标准 Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Pb (.37% in Solder) **Article Safe Usage Statements:** Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # EG8162-000
HL1920E-230V-EURO

Customers Also Bought



TE Part #ZPF000000000006381
951-02H 10-6 P 50

TE Part #ZPF000000000016500
DTS 21 Y 09-35 PN



TE Part #NB18162001
RNF-100-2-BK-STK




TE Part #812836-000
222K121-3-0



TE Part #ZPF000000000018729
FDBA 50H 14-19 PN-K

TE Part #ZPF000000000016511
DTS 21 Y 11-98 PN



TE Part #F92583-000
S200-1-00

TE Part #ZPF000000000016507
DTS 21 Y 11-35 PN



TE Part #ZPF000000000018706
FDBA 50H 10-6 PN-K

TE Part #ZPF000000000002616
402-0140-00

Documents

Product Drawings

B-801-36

English

Product Specifications

Product Specification

English