


PART MARKING GUIDE FOR CIRCULAR BACKSHELLS

THIS DOCUMENT TAKES PRECEDENCE OVER PRODUCTION DRAWINGS (BOM) & CUSTOMER DRAWINGS

OTHER PART MARKING DOCUMENTS IF REQUIRED: -

- DM0044 - PROTECTION CAPS
- DM0050 - MICRO MIN BACKSHELLS
- DM0051 - D-SUB BACKSHELLS
- DM0079 - RAYCHEM PRODUCTS (TXR/200M/BND ONLY)
- DM0107 - 85049 PRODUCTS



AF	ECR-24-223881 (CRN 26424)	21/10/2024	NH	RS
AE	ECR-24-218681 (CRN 26424)	17/09/2024	NH	RS
AD	ECR-24-216466	02/08/2024	NH	RS
REV	DESCRIPTION	DATE	DWN	APVD

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0,40 1 PLC ±0,20 2 PLC ±0,10 ANGLES ±1° ALL FILLETS 0,4 MAX
ALL DIAMETERS	
SURFACE FINISH Ra1,6 MAX REMOVE ALL BURRS AND SHARP EDGES TO 0,1 MAX	




DWN	19/07/2022	MATERIAL	N/A	HEAT TREAT	N/A
CHK	21/07/2022	TE Connectivity			
R.STYLES					
APVD	19/07/2022				
R.MCSHERRY		NAME PART MARK GUIDE FOR CIRCULAR BACKSHELLS (CATALOGUE PARTS)			
SCALE	2:1	SIZE	A3	PART NO	DM0113
SHEET 1 OF 7				REV	AF

PART MARKING GUIDE FOR CIRCULAR BACKSHELLS
THIS DOCUMENT TAKES PRECEDENCE OVER PRODUCTION DRAWINGS (BOM) & CUSTOMER DRAWINGS



CRIB TABLE (USE THIS TABLE TO REFER TO WHICH SHEET FOR MARKING SEQUENCE)										
SERIES	SHEET NO.		SERIES	SHEET NO.		SERIES	SHEET NO.		SERIES	SHEET NO.
11	4		DB	4		100P3249	4		ACSD	7
15	4		DC	4		100P2121	4		S700	4
25	4		DSH	7		100P615	4		DSF	4
34	4		KM	4		100P3214	4		DSF (T3)	7
35	4		KMA	4		100P1703	4		100P275	7
36	4		KMCC	4		PMTAK	6		100P781	4
37	4		GKN	4		PMTAKS (NPT)	7		308	4
39	4		MB	4		PMTAKR (NPT)	7			
51	4		NPF	4		TAK	5			
60	4		NPM	4		100P449	6			
64	4		PAS	4		100P1676	6			
70	4		PGF	4		100P2268	6			
76	4		PVG	4		100P2739	6			
77	4		SIT	4		100P2960	6			
86	4		TMF	4		100P3062	6			
88	4		TMM	4		100P3210	6			
91*	4		VG	4		100P3213	6			
92	4		100P252	4		100P3337	6			
95	4		100P670	4		100P3610	6			
96	4		100P1300	4		100P3623	6			
97	4		100P2682	4		100P3658	6			
98	4		100P3230	7		100P3707	6			
99	4		100P3307	4		100P308	6			
AP	6		100P3738	4		100P1608	4			
APNCJ	4		100P3807LN	4		100P3718	4			
BC	4		100P3807	4		POL3660/17	5			
BT	4		100P1396	4		POL3660/18	5			

* NOTE: FOR ANY SERIES WITH A 'HE' SPRING REFERENCE, IT IS REMOVED FROM THE PART MARKING SEQUENCE;
FOR EXAMPLE FULL PART DESCRIPTION - 91H1-11-05-1-C-HE100
PART DESCRIPTION FOR MARKING - 91H1-11-05-1-C

EXAMPLES OF NUT PROFILES
AND RESPECTIVE MARKING LOCATIONS



S700 NUT EXAMPLE
MARKING LOCATION



EXAMPLE OF WHERE TO FIND THE SERIES CODE
IN THE PART DESCRIPTION:

91H1-11-05-1-C

SERIES
(MINIMUM 2 CHARACTERS LONG, FOUND IN TABLE ABOVE)

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ±0,40 1 PLC ±0,20 2 PLC ±0,10 ANGLES ±1° ALL FILLETS 0,4 MAX

ALL DIAMETERS 0,10	SURFACE FINISH Ra1,6 MAX REMOVE ALL BURRS AND SHARP EDGES TO 0,1 MAX
---------------------	---

DWN K.KUTA-WINCZURA		19/07/2022		MATERIAL N/A		HEAT TREAT N/A			
CHK R.STYLES		21/07/2022		TE Connectivity					
APVD R.MCSHERRY		19/07/2022							
NAME PART MARK GUIDE FOR CIRCULAR BACKSHELLS (CATALOGUE PARTS)									
SCALE 2:1		SIZE A3		PART NO DM0113		SHEET 2 OF 7		REV AF	


PART MARKING GUIDE FOR CIRCULAR BACKSHELLS

SEE NOTES FOR EXEMPTIONS

THIS DOCUMENT TAKES PRECEDENCE OVER PRODUCTION DRAWINGS (BOM) & CUSTOMER DRAWINGS



STYLE 2 (T2) / STYLES 3 (T3) BACKSHELL EXAMPLE
TWO PIECE BACKSHELL ASSEMBLY
ONLY FRONT NUT MUST BE PART MARKED

T2 EXAMPLE




T3 EXAMPLE

USE SAME PARAMETERS AS STATED ON T2 EXAMPLE



EXPLODED VIEW



EXPLODED VIEW

-	SEE SHEET 1	-	-	-
REV	DESCRIPTION	DATE	DWN	APVD


DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0,40 1 PLC ±0,20 2 PLC ±0,10 ANGLES ±1° ALL FILLETS 0,4 MAX
ALL DIAMETERS	
SURFACE FINISH Ra1,6 MAX REMOVE ALL BURRS AND SHARP EDGES TO 0,1 MAX	

DWN	19/07/2022	MATERIAL	N/A	HEAT TREAT	N/A
K.KUTA-WINCZURA		 TE Connectivity			
CHK	21/07/2022				
R.STYLES					
APVD	19/07/2022				
R.MCSHERRY					
NAME PART MARKING GUIDE FOR CIRCULAR BACKSHELLS (CATALOGUE PARTS)					
SCALE	SIZE	PART NO			SHEET
2:1	A3	DM0113			3 OF 7
					REV
					AF

PART MARKING GUIDE FOR CIRCULAR BACKSHELLS

PART MARKING DETAILS TABLE - BACKSHELL SERIES REQUIRING PART NUMBER AND BATCH NUMBER ONLY

SERIES				
11		99		100P670
15		APNCJ		100P1300
25		BC		100P1608
34		BT		100P2682
35		DB		100P3718
36		DC		100P3307
37		DSF		100P3738
39		KM		100P3807LN
51		KMA		100P3807
60		KMCC		100P1396
64		GKN		100P3249
70		MB		100P2121
76		NPF		100P615
77		NPM		100P3214
86		PAS		100P1703
88		PGF		S700
91		PVG		100P781
92		SIT		308
95		TMF		
96		TMM		
97		VG		
98		100P252		



MARKING SEQUENCE

PART DESCRIPTION P*****

***** TO BE REPLACED WITH BATCH NUMBER

NOTE: FOR ANY SERIES WITH A 'HE' SPRING REFERENCE, IT IS REMOVED FROM THE PART MARKING SEQUENCE

FOR EXAMPLE FULL PART DESCRIPTION - 91H1-11-05-1-C-HE100
PART DESCRIPTION FOR MARKING - 91H1-11-05-1-C

EXAMPLE OF WHERE TO FIND THE SERIES CODE IN THE PART DESCRIPTION:

91H1-11-05-1-C

SERIES 91
(MINIMUM 2 CHARACTERS LONG, FOUND IN TABLE ABOVE)

-	SEE SHEET 1	-	-	-
REV	DESCRIPTION	DATE	DWN	APVD


DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ±0,40 1 PLC ±0,20 2 PLC ±0,10 ANGLES ±1° ALL FILLETS 0,4 MAX
ALL DIAMETERS	
SURFACE FINISH Ra1,6 MAX REMOVE ALL BURRS AND SHARP EDGES TO 0,1 MAX	

DWN	19/07/2022	MATERIAL	N/A	HEAT TREAT	N/A
CHK	21/07/2022				
APVD	19/07/2022				
NAME	R.MCSHERRY	PART MARK GUIDE FOR CIRCULAR BACKSHELLS (CATALOGUE PARTS)			
SCALE	2:1	SIZE	A3	PART NO	DM0113
SHEET	4	OF	7	REV	AF

PART MARKING GUIDE FOR CIRCULAR BACKSHELLS

PART MARKING DETAILS TABLE - BACKSHELL SERIES REQUIRING CAGE CODE, PART NUMBER AND BATCH NUMBER

SERIES	CAGE CODE
TAK	U5792
POL3660/17	U5792
POL3660/18	U5792



MARKING SEQUENCE

CAGE CODE PART DESCRIPTION P*****

***** TO BE REPLACED WITH BATCH NUMBER

EXAMPLE OF WHERE TO FIND THE SERIES CODE
IN THE PART DESCRIPTION:

TAKH1-11-05-1-C-SB

SERIES
(MINIMUM 2 CHARACTERS LONG, FOUND IN TABLE ABOVE)

-	SEE SHEET 1	-	-	-
REV	DESCRIPTION	DATE	DWN	APVD

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0,40 1 PLC ±0,20 2 PLC ±0,10 ANGLES ±1° ALL FILLETS 0,4 MAX
ALL DIAMETERS	⌀0,10
SURFACE FINISH Ra1,6 MAX REMOVE ALL BURRS AND SHARP EDGES TO 0,1 MAX	

DWN 19/07/2022		MATERIAL N/A		HEAT TREAT N/A	
CHK 21/07/2022		TE Connectivity			
APVD 19/07/2022					
R.STYLES					
R.MCSHERRY					
NAME PART MARK GUIDE FOR CIRCULAR BACKSHELLS (CATALOGUE PARTS)					
SCALE 2:1	SIZE A3	PART NO DM0113		SHEET 5 OF 7	REV AF

PART MARKING GUIDE FOR CIRCULAR BACKSHELLS

PART MARKING DETAILS TABLE - BACKSHELL SERIES REQUIRING SPECIAL MARKING or LOCATION REQUIREMENTS (N = NO / Y =YES)

SERIES	CAGE CODE	CAGE CODE	PART DESCRIPTION	BATCH NUMBER PREFIX	PREFIX LETTER	BATCH NUMBER	DATE CODE	DATE CODE FORMAT	ADDITIONAL INFORMATION
100P449	N	-	N	N	-	N	N	-	NO MARKING REQUIRED
100P1676	N	-	N	N	-	N	N	-	NO MARKING REQUIRED
100P2268	N	-	N	N	-	N	N	-	NO MARKING REQUIRED
100P2739	N	-	Y	Y	P	Y	N	-	SPECIAL MARKING ON CUSTOMER DRAWING
100P2960	N	-	Y	Y	P	Y	N	-	MARKING LOCATION ON CUSTOMER DRAWING
100P3062	N	-	Y	Y	P	Y	N	-	MARKING LOCATION ON CUSTOMER DRAWING
100P3210	N	-	Y	Y	P	Y	N	-	MARKING LOCATION ON CUSTOMER DRAWING
100P3213	N	-	Y	Y	P	Y	N	-	MARKING LOCATION ON CUSTOMER DRAWING
100P3337	N	-	Y	Y	P	Y	N	-	MARKING LOCATION ON CUSTOMER DRAWING
100P3610	N	-	Y	Y	P	Y	N	-	MARKING LOCATION ON CUSTOMER DRAWING
100P3623	N	-	Y	Y	P	Y	N	-	SPECIAL MARKING ON CUSTOMER DRAWING
100P3658	N	-	Y	Y	P	Y	N	-	MARKING LOCATION ON CUSTOMER DRAWING
100P3707	N	-	Y	Y	P	Y	N	-	MARKING LOCATION ON CUSTOMER DRAWING
100P308	N	-	N	N	-	N	N	-	NO MARKING REQUIRED
AP	N	-	Y	Y	P	Y	N	-	MARKING LOCATION ON CUSTOMER DRAWING
PMTAK	Y	06090	Y	Y	P	Y	N	-	MARKING LOCATION ON CUSTOMER DRAWING

NOTE: - IF THE TEXT LENGTH OF THE MARKING IS TOO LONG TO FIT IN A SUITABLE GAP AS PER THE LOCATION STIPULATED IN THE TABLE ABOVE IN ONE LINE, THEN MULTIPLE LINES CAN BE USED.

EXAMPLE OF WHERE TO FIND THE SERIES CODE IN THE PART DESCRIPTION:

100P1138-14-1-C

SERIES (MINIMUM 2 CHARACTERS LONG, FOUND IN TABLE ABOVE)

-	SEE SHEET 1	-	-	-
REV	DESCRIPTION	DATE	DWN	APVD

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±0,40
1 PLC ±0,20
2 PLC ±0,10
ANGLES ±1°
ALL FILLETS 0,4 MAX

ALL DIAMETERS 0,10

SURFACE FINISH Ra1,6 MAX
REMOVE ALL BURRS AND SHARP EDGES TO 0,1 MAX

DWN 19/07/2022		MATERIAL N/A		HEAT TREAT N/A	
CHK K.KUTA-WINCZURA					
CHK 21/07/2022					
R.STYLES					
APVD 19/07/2022					
R.MCSHERRY					
NAME PART MARK GUIDE FOR CIRCULAR BACKSHELLS (CATALOGUE PARTS)					
SCALE 2:1	SIZE A3	PART NO DM0113		SHEET 6 OF 7	REV AF

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES (TE). IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN TE PERSONNEL, WITHOUT AUTHORIZATION FROM TE (www.TE.com).

DM0113
DWG NO
THIS DRAWING IS A CONTROLLED DOCUMENT

PART MARKING GUIDE FOR CIRCULAR BACKSHELLS (cont.)

USED ON -

PART MARKING DETAILS TABLE - *BACKSHELL SERIES REQUIRING SPECIAL MARKING or LOCATION REQUIREMENTS (N = NO / Y =YES)*

SERIES	CAGE CODE	CAGE CODE	PART DESCRIPTION	BATCH NUMBER PREFIX	PREFIX LETTER	BATCH NUMBER	DATE CODE	DATE CODE FORMAT	ADDITIONAL INFORMATION
PMTAKS (NPT)	Y	06090	Y	Y	P	Y	N	-	MARKING LOCATION ON CUSTOMER DRAWING
PMTAKR (NPT)	Y	06090	Y	Y	P	Y	N	-	MARKING LOCATION ON CUSTOMER DRAWING
100P3230	N	-	Y	Y	P	Y	N	-	MARKING LOCATION ON CUSTOMER DRAWING
ACSD	N	-	Y	Y	P	Y	N	-	MARKING LOCATION ON CUSTOMER DRAWING
DSF (T3)	N	-	Y	Y	P	Y	N	-	MARKING LOCATION ON CUSTOMER DRAWING
DSH	N	-	Y	Y	P	Y	N	-	MARKING LOCATION ON CUSTOMER DRAWING
100P275	N	-	Y	Y	P	Y	N	-	MARKING LOCATION ON CUSTOMER DRAWING

NOTE: - IF THE TEXT LENGTH OF THE MARKING IS TOO LONG TO FIT IN A SUITABLE GAP AS PER THE LOCATION STIPULATED IN THE TABLE ABOVE IN ONE LINE, THEN MULTIPLE LINES CAN BE USED.

EXAMPLE OF WHERE TO FIND THE SERIES CODE IN THE PART DESCRIPTION:

100P1138-14-1-C

SERIES
(MINIMUM 2 CHARACTERS LONG, FOUND IN TABLE ABOVE)

-	SEE SHEET 1	-	-	-
REV	DESCRIPTION	DATE	DWN	APVD

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±0,40
1 PLC ±0,20
2 PLC ±0,10
ANGLES ±1°
ALL FILLETS 0,4 MAX

ALL DIAMETERS

SURFACE FINISH Ra1,6 MAX
REMOVE ALL BURRS AND SHARP EDGES TO 0,1 MAX

DWN19/07/2022
K.KUTA-WINCZURA

CHK21/07/2022
R.STYLES

APVD19/07/2022
R.MCSHERRY

NAMEPART MARK GUIDE FOR CIRCULAR BACKSHELLS
(CATALOGUE PARTS)

MATERIALN/A

HEAT TREATN/A

TE Connectivity

SCALE2:1

SIZEA3

PART NODM0113

SHEET7 OF 7

REVAF