


REVISIONS



THIS DRAWING IS UNPUBLISHED. ALL RIGHTS RESERVED. © COPYRIGHT 20 BY

DIMENSIONS: MILLIMETERS	DWN: I.DIKSAITYTE 14/11/2019	MATERIAL: SEE TABLE 3	FINISH: SEE TABLE 3
	CHK: R.STYLES 19/11/2019	TE Connectivity	
TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD: M.PAUL 14/11/2019		
GENERAL TOL LINEAR $\pm 0,25$ MM ANGULAR $\pm 1^\circ$	PRODUCT SPEC:	NAME:	
	APPLICATION SPEC:	CABLE SEALING BACKSHELL	
	WEIGHT:	SIZE	RESTRICTED TO
	CUSTOMER DRAWING	A4	U5792
		DRAWING NO	REV
		C=P10926	AB
		SCALE	SHEET
		1:1	1 OF 2

REVISIONS

TABLE 1

SHELL SIZE	A THREAD	ØB MAX	ØT MIN	MAX ENTRY	C MAX	D MAX	E MAX	F MAX	K ±0,5	KS ±0,5
08	1/2 - 20 UNF	15,6	6,5	-	16,8	35,8	24,7	36,1	17,5	17,5
10	5/8 - 24 UNEF	18,6	9,2	04	17,0	37,3	26,7	39,1	17,8	18,8
12	3/4 - 20 UNEF	21,7	12,7	06	17,5	38,9	29,2	39,6	18,7	20,4
14	7/8 - 20 UNEF	24,9	14,6	08	18,3	41,1	30,7	41,4	19,0	21,5
16	1 - 20 UNEF	28,2	17,7	10	19,2	43,9	34,2	48,0	21,0	23,0
18	1 1/16 - 18 UNEF	30,9	19,7	12	19,4	48,8	37,2	50,8	23,5	24,0
20	1 3/16 - 18 UNEF	34,1	22,9	16	20,3	50,1	42,2	50,8	27,0	25,7
22	1 5/16 - 18 UNEF	37,3	26,1	16	20,5	52,6	44,2	50,8	27,0	27,2
24	1 7/16 - 18 UNEF	40,4	29,0	16	22,0	54,0	45,2	50,8	27,0	28,7
28	1 3/4 - 18 UNS	50,0	35,0	24	23,5	55,0	54,4	55,1	31,4	31,6
32	2 - 18 UNS	56,3	41,3	28	24,9	56,0	61,0	56,1	36,4	33,5
36	2 1/4 - 16 UN	62,7	46,8	32	26,4	57,0	67,5	57,7	38,0	36,0

IF MAX ENTRY IS EXCEEDED, ADAPTOR ASSEMBLY WILL BE SUPPLIED AS TYPE 2, IN WHICH CASE DIMENSIONS C, D, E, F, K & KS DO NOT APPLY AND MIN L IS L3

TABLE 2


ENTRY SIZE	CABLE RANGE
04	3,2 - 7,9
06	6,4 - 11,1
08	9,8 - 14,3
10	8,9 - 15,9
12	12,7 - 19,1
16	15,9 - 23,8
20	22,2 - 31,8
24	25,4 - 34,9
28	31,8 - 41,3
32	36,5 - 47,6

TABLE 3

CODE	MATERIAL / FINISH
1-C	ALUMINIUM / ELECTROLESS NICKEL
1-B	ALUMINIUM / CADMIUM OLIVE DRAB OVER ELECTROLESS NICKEL
46-J	STAINLESS STEEL 316 / PASSIVATE
1-G	ALUMINIUM / BLACK ANODISE SULPHURIC, PER MIL-A-8625, TYPE II, CLASS 3
1-ZB	ALUMINIUM / ZINC COBALT OLIVE DRAB OVER ELECTROLESS NICKEL
1-ZN	ALUMINIUM / ZINC NICKEL BLACK PASSIVATE OVER ELECTROLESS NICKEL
4-J	STAINLESS STEEL / PASSIVATE
2-Z	NICKEL ALUMINIUM BRONZE / SHOT BLAST

SEE SS0076 FOR FULL RANGE OF FINISH OPTIONS

37A1-16-08-1-C-CC-L3





RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

© COPYRIGHT 20 BY

DIMENSIONS: MILLIMETERS	DWN: I.DIKSAITYTE 14/11/2019	MATERIAL: SEE TABLE 3	FINISH: SEE TABLE 3
	CHK: R.STYLES 19/11/2019	 TE Connectivity	
TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD: M.PAUL 14/11/2019		
GENERAL TOL LINEAR ±0,25MM ANGULAR ±1°	PRODUCT SPEC: -	NAME: CABLE SEALING BACKSHELL	
	APPLICATION SPEC: -	SIZE: A4	CAGE CODE: U5792
	WEIGHT:	DRAWING NO: C-P10926	RESTRICTED TO
	CUSTOMER DRAWING	SCALE: 1:1	SHEET: 2 OF 2
		REV: AB	