



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUL 2021 (219) SVHC > Threshold: Pb (.3% in BODY & NUT) Cd (3% in BODY & NUT) Article Safe Usage Statements: Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought






TE Part #903960-000
222K163-25/225-0



TE Part #2161213004
55A0111-16-2



TE Part #2820403012
44A0111-24-0



TE Part #CQ50483001
RAY-101-7.5(10)



TE Part #216027-008
55A0111-26-9



TE Part #181271-2
MOD 2 CONTACT REC.




TE Part #1-215083-8
MICRO-MATCH MOW.18P



TE Part #1-338068-8
MICRO-MATCH FTE,18P



TE Part #2-1623730-4
BCHE 4 W 68R 5%



TE Part #F013703001
44A0111-12-0CK0001

Documents

Product Drawings
BNX40AB00-2212AX

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_CU4384-000_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_CU4384-000_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_CU4384-000_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



5-1654025-5_sec6_Adapters

English

Circular Backshells

English

Product Specifications

General Information Package for BNDXXA (Band Strap) Adapters

English

Product Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English