



a) Part as supplied

203W301-25L-G04



b) Part after unrestricted recovery



DIMENSIONS (in millimetres)

Part No.	H		J		P	R	S	T	JO	HW	JW	U
	Min a	Max b	Min a	Max b	±10% b	±10% b	±10% b	±10% b	±10% b	±20% b	±20% b	±20% b
203W301-25L-G04	10 (0.39)	5.8 (0.23)	10 (0.39)	2.2 (0.09)	29 (1.14)	21 (0.83)	2.0 (0.08)	0.5 (0.02)	4.5 (0.18)	0.5 (0.02)	0.5 (0.02)	1.6 (0.06)

Copyright(!)

The copyright in this drawing is the property of TE Connectivity. The drawing is issued on the condition that it is not copied, reproduced or disclosed to a third party, either in whole or in part without the prior written consent of TE Connectivity.

Drawn N. NAGAR Checked Issue 1 Date 16/03/2015

 Conforms to ISO Recommendations
 3rd Angle Projection
 Not to Scale

Approval Design MKTG. Q.A.

