



BB2/70RS

SURFACE MOUNT
 Beam Mount Loudspeaker System,
 8" O.D. Speaker, 4W-70V Rotary Select Transformer

GENERAL DESCRIPTION

The **BB2/70RS** is a complete, beam mount loudspeaker system consisting of an 8C10PAX - 8" O.D. dual cone loudspeaker with a 10 oz. magnet, 4W-70V rotary select transformer mounted on a round, studded baffle, and two (2) beam clamps attached to a round, steel backbox. White powder coat finish.

INTENDED USE - Indoor Environment



Program Material	Signal tones, voice, and music
Installation	Downward Firing on a Steel "I" Beam of 5.25" Maximum Width

AUDIO SPECIFICATIONS

Average Sensitivity	95 dB SPL, 1W/ 1M
Loudspeaker Power Rating	20W RMS, EIA 426A Standard
Calculated Output	102 dB SPL, 5W/ 1M
Magnet Type & Weight	BeFe Ceramic, 10 oz. Nominal
Frequency Response	65Hz - 17kHz EIA 426A Standard
Nominal Coverage Angle	90° Included Angle, -6 dB / 2 kHz, Half space
Audio Connection	7" Leads

SYSTEM COMPONENTS

Loudspeaker	8C10PAX
Transformer	4W-70V : 5 tap (4W, 2W, 1W, 0.50W, 0.25W)



Ø12516