


Flat

SPECIFICATIONS
1. ELECTRICAL:
UL APPLICATIONS: 250 VOLTS AC MAX. AT 2 AMPS.
DIELECTRIC WITHSTANDING VOLTAGE : 1000 VOLTS AC.
INSULATION RESISTANCE: 100 M Ω.
TERMINATION: RESISTANCE 20m Ω MAX AFTER ENVIRONMENTAL TESTING.
2. MECHANICAL:
CABLE-TO-PLUG TENSILE STRENGTH : 19.6N/PCS MIN.
DURABILITY : 200 MATING CYCLES.
3. MATERIAL & FINISH:
HOUSING: POLYCARBONATE, UL94V-0 OR UL94V-2.
COLOR : TRANSPARENT OR OTHER COLOR ARE AVAILABLE.
CONTACT BLADE: COPPER ALLOY.
CONDUCTOR : SOLID WIRE, .24AWG, 26 AWG.
GOLD PLATING: 15u".



BLADE:	B
Drawing	
Mark	

REV	DATE	MODIFICATION	DRAWN
2013/09/05			

Quest Technology International, Inc. 11200 NW 138th St. Medley, FL 33178			
DIMENSION IN mm (Inch) TOLERANCE UNLESS OTHERWISE SPECIFIED		MATERIAL	图号
.X±0.20		PC	NMP-6111
.XX±0.10		.X°±5°	名称
.XX±2°		MODULE PLUG 8P8C FOR FLAT CABLE.	图号
审核	核对	制图	比例
APPROVAL	CHECKED	Cathylia	SCALE 2/1
			角注
			PROJ.
			张数
			更改
			REV
			A