






MATERIAL

MAIN BODY : CARBON STEEL.
REPLACEABLE BLADE : ALLOY STEEL.
FINISHED: BLACK OXIDE FINISHED.
KEYSTONE SOCKET : PC+ABS HIGH-IMPACT UL94V-0 THERMOPLASTIC.
HANDLES : PVC.
WEIGHT : 380g ±20g.
SUITABLE MODEL : EM SERIES / EQ SERIES.

PHYSICAL CHARACTERISTICS

REPLACEABLE BLADE : 2000 TERMINATION CYCLES.
CONTACT COMPATIBILITY : ACCOMMODATES 22 TO 24 AWG SOLID.
STORAGE TEMPERATURE RANGE : -15°C TO 50°C.
HUMIDITY : 10%~90%RH.



Scale		1:2						Quest Technology Int'l, Inc. 11200 NW 138th St., Medley, FL 33178	
3rd Angle Projection									
Unit		mm		Part No. TEL-6060					
Date		2011/11/25		Title: Keystone Jack Dual Crimping Tool for Quest Slim-Style Keystone Jacks					
Tolerance									
~20	~50	~150	150~	ANGLE	Drawn by	Checked by	Drawing No.		
±0.2	±0.4	±0.5	±1.5	±2°	Ted		DCDL807EMQ010		