




[Products](#) ▾ | [Documentation](#) ▾ | [Resources](#) ▾ | [My Account](#) ▾ | [Customer Support](#)

521076-000 Product Details



521076-000

TE Internal Number: 521076-000

 [Active](#)

Shield Terminators

 [Always ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- Fluid Resistance = Splash Protection
- Cable Temperature Rating = 125 °C
- Jacket Outer Diameter = 1.50 - 3.60 mm
- Shield O.D. (Min.) = 1.00 - 3.20 mm
- With Preinstalled Lead

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)

[Request Sample](#)

[Find Similar Products](#)

[Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [Coaxial Solder Sleeve Device with Pre-installed Lead](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Mechanical Attachment:

- Inside Diameter (mm [in]) = 3.70 [0.145]

Body Related Features:

- Fluid Resistance = Splash Protection
- [Jacket Outer Diameter \(mm \[in\]\)](#) = 1.50 – 3.60 [0.060 – 0.140]

Housing Related Features:

- [Shield O.D. \(Min.\) \(mm \[in\]\)](#) = 1.00 – 3.20 [0.040 – 0.125]
- [Preinstalled Lead](#) = With
- Preinstalled Lead Wire Size (mm² [AWG]) = 0.61 [20]
- MIL or NAS Specification (MIL-S-83519) (NAS 1747) = No
- Length (Max.) (mm [in]) = 21.50 [0.850]

Configuration Related Features:

- Temperature Indication System = Without

Industry Standards:

- [RoHS/ELV Compliance](#) = ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was ELV compliant

Conditions for Usage:

- [Cable Temperature Rating \(°C\)](#) = 125
- Operating Temperature (Max.) (°C) = 125

Other:

- Brand = Raychem



[Provide Website Feedback](#) | [Need Help?](#)

[Home](#) | [Customer Support](#) | [Suppliers](#) | [Site Map](#) | [Privacy Policy](#) | [Browser Support](#)

© 2009 Tyco Electronics Corporation All Rights Reserved