



TE Connectivity: Every Connection Counts
© 2015 TE Connectivity Ltd. family of companies. All Rights Reserved

+ HARNESSING



HEAT-SHRINK BOOTS



✓ Active

↓ **PRODUCT DRAWING**
English

TE CONNECTIVITY (TE)
202K153-25L-0
Raychem

CV7373-000
TE Internal Number: CV7373-000

Always EU RoHS/ELV Compliant

Connector or Backshell Outside Diameter **1.02 in, 1.1 in, 1.18 in, 1.26 in, 26 mm, 28 mm, 30 mm, 32 mm**

Wire/Cable Outside Diameter **.35 in, .39 in, .43 in, .47 in, .55 in, .63 in, 10 mm, 11 mm, 12 mm, 14 mm, 16 mm, 9 mm**

Lipped **Yes**

Operating Temperature Range (°C) **-75 – 150**

Adhesive Options **S1125 Separate Adhesive, -75°C – 150°C (-103°F – 302°F)**

Product Drawings

BOOT, STRAIGHT, SPECIFICATION CONTROL DRAWING
PDF
English

Product Environmental Compliance

[EPS Heat Shrinkable Polymeric Products](#)

PDF
English

[EPS Heat Shrinkable Polymeric Products](#)

PDF
French

[EPS Heat Shrinkable Polymeric Products](#)

PDF
German

[EPS Heat Shrinkable Polymeric Products](#)

PDF
Italian

[EPS Heat Shrinkable Polymeric Products](#)

PDF
Norwegian

[EPS Heat Shrinkable Polymeric Products](#)

PDF
Spanish

[EPS Heat Shrinkable Polymeric Products](#)

PDF
Swedish

[EPS Heat Shrinkable Polymeric Products](#)

PDF
Dutch

[EPS Heat Shrinkable Polymeric Products](#)

PDF
Danish

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features	Molded Part Type	Molded Boot (Light Weight)
Configuration Features	Lipped	Yes
Body Features	Material Systems Code	25
	Adhesive Pre-Coat	No
	Entry Size (Braided or Magneform Adapter)	12, 13, 14, 15
	Entry Size (Solid or Fixed Adapter)	8
	Entry Size (Tinel-Lock Adapter)	10, 12, 14
	Entry Size (Spin Coupling Adapter)	12
	Material	Light wght fluid resistant modified elastomer
Dimensions	Connector or Backshell Outside Diameter	1.02 in, 1.1 in, 1.18 in, 1.26 in, 26 mm, 28 mm, 30 mm, 32 mm

Wire/Cable Outside Diameter **.35 in, .39 in, .43 in, .47 in, .55 in, .63 in, 10 mm, 11 mm, 12 mm, 14 mm, 16 mm, 9 mm**

Cable Diameter Range **8.4 – 19mm [.331 – .748 in]**

Usage Conditions Operating Temperature Range (°C) **-75 – 150**

Operation/Application Power Cable Accessory **No**

Other Adhesive Options **S1125 Separate Adhesive, -75°C – 150°C (-103°F – 302°F)**

Adhesive Type **Adhesive Purchased Separately**

Product Compliance

[Statement of Compliance](#)
PDF

[VIEW ALL PRODUCT COMPLIANCE](#)