

Data sheet

PT091xxVGBN Typ 373

Page 1/6


P/N
313731xx

xx=number of poles


2020/07/22

Version: R


Illustrations



Dimensional drawing



Drill pattern



See enlarged drawings at the end of document

Product specification



- pin header, solderable
- centerline 2.50 mm, direction of connection vertical 0°
- closed ends
- color green

Technical Data

General Data

Solder pin length	3.2 mm		
Min. number of poles	2		
Max. number of poles	12		
Insulating material class	CTI 600		
clearance/creepage dist.	1.7 mm		
Protection category	IP00		
Rated current	4 A		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Rated voltage	80 V	320 V	320 V
Rated test voltage	2.5 kV	2.5 kV	2.5 kV

Approvals

 V / A	150 / 5
approval UL - File No.	E121004
 1.5 mm ²	80 V / 2.5 kV / 6 A / 0.8 x 0.8 mm

Material

Insulating material	PA66
Flammability class	V0
Contact pin material	CuFe
Contact pin surface	Ni + Sn
Glow-Wire Flammability GWFI	960 °C acc. to IEC 60695-2-12
Glow-Wire Flammability GWIT	775 °C acc. to IEC 60695-2-13

Climatic Data

Upper limit temperature	105 °C
Lower limit temperature	-40 °C

general

Tolerance	ISO 2768 -mH
Solderability	Acc. to JEDEC JESD22-B102E 245°C/5s

Accessories

P/N	Designation
720062-01-8	F_Kodier_ASP051_rtf

© 2020 METZ CONNECT - Technische Änderungen vorbehalten! Subject to modifications! Sous réserve de modifications techniques!



U | Contact

Data sheet PT091xxVGBN Typ 373

Page 4/6

P/N
313731xx

xx=number of poles

2020/07/22

Version: R


Counterpart of

P/N	Designation
ASP051	SP051xxVGNN ASP051



Illustrations

Dimensional drawing



$L = (\text{pole size} - 1) \times \text{centerline} + 4.4 \text{ mm} [0.173]$

Illustrations

Drill pattern

