




Headers

to ASP046

	Type 178	page 148
	Type 179	page 144
	Type 219	page 143
	Type 220	page 144
	Type 229	page 147
	Type 230	page 148
	Type 286	page 146
	Type 288	page 150
	Type 290	page 146
	Type 292	page 150

Accessories

for ASP046

(only in combination with headers type 178, 179, 219, 220, 229 and 230)

coding set

700025 page 206

ASP046

Spring clamp terminal block, pluggable, centerline 5.08 mm / 0.200 inches, wire entry parallel to plug direction

Technical Data

V / A / AWG 300 / 8 / 28 - 16

0.08 - 1.5 mm² 450 V / 4 kV / 10 A

Insulation co-ordination according to EN 60664-1

Clearance and creepage distances min. 4 mm

Insulating material class CTI 400

Overvoltage category III III II

Pollution degree 3 2 2

Rated voltage 250 500 500

Rated test voltage 2.5 4 2.5

Protection category according to IEC 529


Min. insul. strip length IP20 4 mm

Pole size 2 - 24

Colour black

Dimensions in mm

1 mm = 0.0394 in.



$L = (\text{pole size} - 1) \times \text{centerline} + 5 \text{ mm} / 0.197 \text{ inches}$

Part numbers (P/N)

(information: page 16)

Complete the part number by adding the pole size.

ASP046

centerline 5.08 mm / 0.200 inches

P/N ASP046

	02	03	04	05	06	07	08
09	10	11	12	13	14	15	16
17	18	19	20	21	22	23	24

ASP04A

centerline 10.16 mm / 0.400 inches

P/N ASP04A

	02	03	04	05	06	07	08
09	10	11	12				

* approval pending

Standard pole sizes

Available on demand. Minimum order quantity 5000 pieces per item.