



B-041-28-2N Product Details

[Share](#) [Print](#) [Email](#)


Active

Solder Sleeve Wire Splices

B-041-28-2N

B-041-28-2N

TE Internal Number: 224633-000

Product Highlights [View All](#)

- Coaxial Terminator
- Splice Type = Solder Sleeve
- Fluid Resistance = Splash Protection
- Wire Temperature Rating Range (Max.) = 125°C
- Inside Diameter = 4.40 mm

[Pricing & Availability](#)
[Request Sample](#)
[Add to My Part List](#)
[Buy Product through Distributor](#)
[Feedback](#)
[Documents](#)
[Features](#)
[Compliance](#)

Please Note:

Use the Product Drawing for all design activity

Product Type Features

Product Type	Coaxial Terminator
Splice Type	Solder Sleeve

Termination Features

Connection Type	Solder
-----------------	--------

Dimensions

Inside Diameter (mm [in])	4.40 [0.173]
Inside Diameter Fully Recovered (mm [in])	1.80 [0.071]
Length (mm [in])	30.00 [1.181]

Industry Standards

RoHS/ELV Compliance	Not ELV/RoHS compliant
Lead Free Solder Processes	Not relevant for lead free process

Environmental

Fluid Resistance	Splash Protection
Operating Temperature (Max.) (°C)	150

Conditions for Usage

Wire Temperature Rating Range (Max.)	125°C
--------------------------------------	-------

Operation/Application

Application	Coaxial Cable Termination
-------------	---------------------------

Other

Brand	Raychem
Node Classification	Coax Cable Termination

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)
- [Global Accessibility Statement](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

