




## 22759/32-26-5 Product Details

[Share](#) | [Print](#) | [Email](#)


22759/32-26-5

TE Internal Number: 982620-000

**Active**

### Spec 44, Spec 55 and Spec RCW Wire and Cable

**Always EU RoHS/ELV Compliant** ([Statement of Compliance](#))

#### Product Highlights:

- Cable Type = Spec 55
- Wire Source = United States
- Cable Style = Primary
- Wire Size (AWG/CM) = 26 AWG
- Voltage Rating = 600 VAC

[View all Features](#)

#### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

#### Documentation & Additional Information

##### Product Drawings:

- [Wire, Radiation-Crosslinked, Modified, ETFE-Insulate...](#) (PDF, English)

##### Catalog Pages/Data Sheets:

- None Available

##### Product Specifications:

- None Available

##### Application Specifications:

- None Available

##### Instruction Sheets:

- None Available

##### CAD Files:

- None Available

##### Related Products:

- [Tooling](#)

[List all Documents](#)

#### Product Features (Please use the Product Drawing for all design activity)

##### Product Type Features:

- [Cable Type](#) = Spec 55
- [Cable Style](#) = Primary
- Number of Conductors = 1

##### Electrical Characteristics:

- Voltage Rating (VAC) = 600

##### Body Features:

- Wire Size (AWG/CM) = 26 AWG
- Conductor Type = Tin-Plated Copper
- Wire Color = Green
- Nominal Outside Diameter (mm [in]) = 0.81 [0.032]
- Wire Diameter (mm [in]) = 0.81 [0.032]
- Conductor O.D. (mm [in]) = 0.50 [0.020]

##### Industry Standards:

- Government/Industry Qualification = Yes
- Government/Industry Part Number = M22759/32-26-5
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

##### Conditions for Usage:

- Temperature Range (°C) = -65 - +150
- Wire Size - Details = 26 AWG 0.15 mm<sup>2</sup>, 0.00024 in<sup>2</sup>, 19 x 38 AWG

##### Operation/Application:

- Application = General Purpose - Lightweight

##### Packaging Features:

- Wire Source = United States

##### Other:

- Brand = Raychem

#### Corporate Information

[Who We Are](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)

#### Quick Links

[Check Distributor Inventory](#)  
[Cross Reference](#)  
[Find Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

#### Customer Support

[Email or Chat With Us](#)  
[Find a Phone Number](#)  
[Search Knowledge Base](#)  
[Manage your Account](#)

#### Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

