

Data sheet

OpDAT Industry LC-D SM adapter insert

P/N

1402L00820MI


EAN 4250184115908

2015-19-06

Illustrations



Dimensional drawing



See enlarged drawings at the end of document

Product specification

- LC-D coupler
- slotted ceramics sleeve for single mode applications
- slotted metal sleeve (Ph-Br) for multi mode applications
- conformity with relevant IEC framework specifications with regard to testing conditions and connector compatibility to connector version LC to IEC 61754-20
- compliance with EN 50173-1:2011-09 and ISO/IEC 24702 with regard to limit values for insertion loss
- flame-retardant and halogen-free plastic housing
- flame-retardant and halogen-free dust cover
- in flange or wall outlet of var. 1 and 4 - suitable for integration
- variant 14 only available in sets
- Service life: min. 500 plug-in cycles
- operating temperature -40 °C to +70 °C
- variants: blue (SM), beige (MM)



Data sheet

Page 2/4

OpDAT Industry LC-D SM adapter insert

P/N

1402L00820MI

EAN 4250184115908

2015-19-06

Technical Data

General Data

Design	Adapter
Transmission technology	Fiber optic
Color	blue
Dimensions	
Dimension (L x W x H)	30.90 x 15.60 x 13.20 mm
Dimension (L x W x H)	1.22 x 0.61 x 0.52 in.
Mode type of the fiber	Single mode
Labeling option	on housing

Connections/interfaces

Connector technology interface 1	LC-D
Connector technology interface 2	LC-D
Number of ports interface 1	1
Number of ports interface 2	1
Number of equipped ports interface 1	1
Number of ports interface 2 equipped	1
Number of ports with dust protection interface 1	1
Number of ports with dust protection interface 2	1

Mechanical characteristics

Cut-out	SC, LC-D, E2000
Connector type	Duplex
Life - Number of mating cycles	min. 1000
Position/mounting of latch - standard installation position	top

Materials and material properties

Material - Housing	Plastics
Material - Sleeve	ceramic, slotted
Material - Dust protection	flame-retardant and halogen free



OpDAT Industry LC-D SM adapter insert

P/N

1402L00820MI

EAN 4250184115908

2015-19-06

Technical Data

Environmental conditions

Temperature (min. - max.)

Temperature - Operating °C -40 - 70 °C

Temperature - Operating °F -40 - 158 °F

Certifications

Gost Certification yes

Approvals

RoHS compliant

The product meets the following standards

Generic cabling systems

General requirements DIN EN 50173-1:2011-09

Industrial area ISO/IEC 24702 AMD 1 | DIN EN 50173-3: 2011-09
TIA/EIA 1005

Classifications

ETIM 5.0 EC000752

Packing details

Type of packaging 10 pc(s) / box

Packaging unit - Weight (gram) 91.00 g

Packaging unit - Weight (pound) 0.20 lb

Packaging dimension (D x W x H) 89.00 x 250.00 x 105.00 mm

Packaging dimension (D x W x H) 3.50 x 9.84 x 4.13 in.



Data sheet

Page 4/4

OpDAT Industry LC-D SM adapter insert

P/N

1402L00820MI

EAN 4250184115908

2015-19-06

Illustrations

Dimensional drawing

