

## Data sheet

OpDAT REGplus 6xSC/ST-D MM (Ph-Br), 1xM20, with shrink splice holder P/N  
150240C30610S


EAN 4250184152583

2015-28-05

### Illustrations



Dimensional drawing



See enlarged drawings at the end of document

### Product specification

- splice distributor for TH35 rail
- equipped with SC-D/ST-D (MM) couplers made of zinc die-casting
- slotted metal sleeve (Ph-Br) for multi mode applications
- with fiber reservoir
- custom-labeled identification strips
- various mounting versions on rail
- splice tray with shrink splice holder
- front plate can be completely removed
- cable feed from top or bottom, straight or inclined, with M20 cable gland (up to 2 possible)
- feed of preassembled cables is possible
- one cable gland M20 with strain relief included in the delivery
- housing cover fastening by means of just one captive screw
- unoccupied coupler recesses are closed with special blind plugs
- variants: equipped with 2, 3, 4 or 6 SC-D/ST-D couplers (SC-D interior, ST-D exterior)
- please note: if you use preassembled cables with ST plugs, use the unequipped version of the OpDAT REG plus. The ST-D couplers required in this case are available as accessory. Before mounting the couplers in the housing, plug the preassembled ST plugs in the couplers for reasons of space.

**OpDAT REGplus 6xSC/ST-D MM (Ph-Br), 1xM20, with shrink splice holder P/N**

150240C30610S

EAN 4250184152583

2015-28-05

**Technical Data**

**General Data**

Fields of application	Structured building cabling
Design	Splice distributor
Mounting style	Standard rail TH35
Color	gray
Dimensions	
Dimension (L x W x H)	144.80 x 143.80 x 37.00 mm
Dimension (L x W x H)	5.70 x 5.66 x 1.46 in.
Mode type of the fiber	Multimode
Labeling option	identification label

**Connections/interfaces**

Connector technology interface 1	SC-D/ST-D Couplers
Connector technology interface 2	SC-D/ST-D Couplers
Number of ports interface 1	6
Number of ports interface 2	6
Number of equipped ports interface 1	6
Number of ports interface 2 equipped	6
Number of ports with dust protection interface 1	6
Number of ports with dust protection interface 2	6
Cable access/outlet	from top or bottom, straight or inclined

**Mechanical characteristics**

Cut-out	SC-D, LC-Q, ST-D
Connector type	Duplex
Life - Number of mating cycles	min. 500
Strain relief	M Verschraubung

**Materials and material properties**

Material - Coupler housing	GD-Zn (zinc die-cast)
Material - Front cover	Frianyl
Material - Sleeve	PhBr, slotted

© 2015 METZ CONNECT - Technische Änderungen vorbehalten! Subject to modifications! Sous réserve de modifications techniques!



**OpDAT REGplus 6xSC/ST-D MM (Ph-Br), 1xM20, with shrink splice holder** P/N

150240C30610S

EAN 4250184152583

2015-28-05

**Technical Data**

**Certifications**

Gost Certification yes

**Approvals**

RoHS compliant

**Classifications**

ETIM 5.0 EC001130

**Packing details**

Type of packaging	1 pc(s) / box
Packaging unit - Weight (gram)	706.00 g
Packaging unit - Weight (pound)	1.56 lb
Packaging dimension (W x H x D)	145.00 x 182.00 x 40.00 mm
Packaging dimension (W x H x D)	5.71 x 7.17 x 1.57 in.

© 2015 METZ CONNECT - Technische Änderungen vorbehalten! Subject to modifications! Sous réserve de modifications techniques!



Data sheet

Page 4/5

**OpDAT REGplus 6xSC/ST-D MM (Ph-Br), 1xM20, with shrink splice holder** P/N

150240C30610S

EAN 4250184152583

2015-28-05

## Accessories

P/N	Designation
899789-01	Label sheet for E-DAT C6 and E-DAT design patch panels



## Illustrations

Dimensional drawing

