




# 44A0121-22-2/9-MX Product Details

[Share](#) | [Print](#) | [Email](#)


✔ Active

## Spec 44, Spec 55 and Spec RCW Wire and Cable

44A0121-22-2/9

**44A0121-22-2/9-MX** ✔

TE Internal Number: 382314-002

### Product Highlights [View All](#)

- Cable Type = Spec 44
- Wire Source = United States
- Cable Style = Primary
- Wire Size (AWG/CM) = 22 AWG
- Voltage Rating = 600 VAC

[Pricing & Availability](#)
[Request Sample](#)
[Add to My Part List](#)
[Buy Product through Distributor](#)
[Feedback](#)
[Documents](#) | [Features](#) | [Compliance](#)

#### Please Note:

Use the Product Drawing for all design activity

Product Type Features		Industry Standards	
Cable Type <sup>?</sup>	Spec 44	Government/Industry Qualification	No
Cable Style <sup>?</sup>	Primary	RoHS/ELV Compliance <sup>?</sup>	RoHS compliant, ELV compliant
Electrical Characteristics		Lead Free Solder Processes <sup>?</sup>	Not relevant for lead free process
Voltage Rating (VAC)	600	RoHS/ELV Compliance History	Always was RoHS compliant
Dimensions		Conditions for Usage	
Conductor Outer Diameter (mm [in])	0.79 [0.031]	Temperature Range (°C)	-65 - +150
Body Features		Wire Size - Details	22 AWG 0.38 mm <sup>2</sup> , 0.00059 in <sup>2</sup> , 19 x 34 AWG
Wire Size (AWG/CM)	22 AWG	Operation/Application	
Conductor Type	Tin-Coated Copper	Application	General Purpose - Light Weight
Wire Color	Red, White	Packaging Features	
Nominal Outside Diameter (mm [in])	2.39 [0.094]	Wire Source	United States
Wire Diameter (mm [in])	1.19 [0.0468]	Other	
Configuration Features		Brand	Raychem
Number of Conductors	Twisted Pair	Node Classification	Twisted Pair Cable

#### Related Products

Not quite the product you're looking for?  
[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)