

Data sheet

Page 1/4


OpDAT REGpro front cover 3RU, 7HP 6xE2000 DC SM APC (ceramic) P/N

15024A5C06-E


EAN 4250184141723

2015-15-06

Illustrations



Dimensional drawing



See enlarged drawings at the end of document

Product specification

- front plate 3RU/HPE with 6 E2000 DC couplers
- slotted ceramics sleeve for single mode and multi mode applications
- suitable for mounting in OpDAT REG pro and OpDAT REGpro24
- gray, powder-coated steel sheet
- variants: 6xE2000 DC (blue), 6xE2000 DC APC (green), 6xE2000 DC (beige)

Data sheet

Page 2/4

OpDAT REGpro front cover 3RU, 7HP 6xE2000 DC SM APC (ceramic)

P/N

15024A5C06-E

EAN 4250184141723

2015-15-06

Technical Data

General Data

Fields of application	Structured building cabling
Design	Front cover
Mounting style	3RU/7HP
Transmission technology	Fiber optic
Color	green
Dimensions	
Dimension (L x W x H)	43.75 x 128.90 x 35.30 mm
Dimension (L x W x H)	1.72 x 5.07 x 1.39 in.
Height unit	3RU
Horizontal pitch	7Units
Mode type of the fiber	Single mode
Special features	Connection technology: for fusion splice or pre-assembled cable

Connections/interfaces

Connector technology interface 1	E2000 DC Couplers
Connector technology interface 2	E2000 DC Couplers
Number of ports interface 1	6
Number of ports interface 2	6
Number of equipped ports interface 1	6
Number of ports interface 2 equipped	6
Number of ports with dust protection interface 1	6
Number of ports with dust protection interface 2	6

Mechanical characteristics

Cut-out	E2000 DC
Life - Number of mating cycles	min. 1000

Materials and material properties

Material - Coupler housing	Plastics
Material - Mounting plate	steel
Material - Mounting plate finish	powder-coated
Material - Sleeve	ceramik, slotted



Data sheet

Page 3/4

OpDAT REGpro front cover 3RU, 7HP 6xE2000 DC SM APC (ceramic)

P/N

15024A5C06-E

EAN 4250184141723

2015-15-06

Technical Data

Certifications

Gost Certification yes

Approvals

RoHS compliant

The product meets the following standards

Fibre optic connector interfaces DIN EN 61754-15

Classifications

ETIM 5.0 EC001130

Packing details

Type of packaging	1 pc(s) / box
Packaging unit - Weight (gram)	274.00 g
Packaging unit - Weight (pound)	0.60 lb
Packaging dimension (W x H x D)	145.00 x 182.00 x 40.00 mm
Packaging dimension (W x H x D)	5.71 x 7.17 x 1.57 in.



Illustrations

Dimensional drawing

