

Terminals & Splices > Splices

# D-200-0237-RT

D-200-0237-RT



Raychem

TE Internal #: **EG3867-000**

TE Internal Description: **D-200-0237-RT**

Product Type : **SolderShield Splice Kit**

Terminal & Splice Type : **Splice**

Wire Size (AWG): **20 – 16**

Sealable : **Yes**

Splice Capacity : **2**

[Digital Datasheet](#)

[Compatible Parts & Tooling](#)

### We are here to help!

Get in touch with our product experts.



CHAT WITH US



EMAIL US



CALL US

Feedback

## Documents

## Features

## Product Compliance

### Product Drawings

Dimensional Drawing  
D-200-0237-RT

[D-200-0237-RT](#) English

### Datasheets & Catalog Pages

1654025\_Sec8\_D-200

[ENG\\_CS\\_1654025\\_Sec8\\_D-200\\_0313.pdf](#)

English

### Product Environmental Compliance

REACH Substance Communication Document

[ENG\\_PC\\_RSCD\\_HBCDD\\_1.pdf](#) English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type  
Features

Product Type : **SolderShield Splice Kit**  
Sealable : **Yes**  
Splice Type : **Immersion Resistant Splice**  
Serrated : **No**  
Accessory Type : **Splice**  
Barrel Type : **Closed Barrel**  
Wire/Cable Type : **Shielded Cable**

Configuration  
Features

Splice Capacity : **2**

Body Features

Splice Features : **Splice Kit**  
Splice Material : **Nickel-Plated**

Contact Features

Terminal & Splice Type : **Splice**

Dimensions

Wire Size (AWG): **20 – 16**

Usage Conditions

Operating Temperature Range : **-65 – 200 °C [ -85 – 392 °F ]**

Operation/Application Heavy Duty : **No**

Industry  
Standards

Government Qualified : **No**

Packaging  
Features

Packaging Method : **Bag/Box**

EU RoHS  
Directive  
2011/65/EU

*This declaration covers EU Directive 2011/65/EU incl. Delegated Directive 2015/863/EU. The restrictions under 2015/863/EU apply as of 22 July 2021 for EEE categories 8 (medical devices) and 9 (monitoring and control equipment).*

EU ELV Directive  
2000/53/EC

China RoHS 2  
Directive MIIT  
Order No 32, 2016

EU REACH  
Regulation (EC)  
No. 1907/2006

Current ECHA Candidate List: **JUL 2019 (201)**  
Candidate List Declared Against: **JAN 2019 (197)**  
HBCDD (3% in Flux)

Halogen Content



Solder Process Capability	Not applicable for solder process capability
Statement of Compliance	<a href="#">Statement of Compliance pdf</a>
Compliance Documents	There may be Environmental Compliance related documents on the <a href="#">DOCUMENTATION Tab</a>
Disclaimer	<p>This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <a href="https://echa.europa.eu/guidance-documents/guidance-on-reach">https://echa.europa.eu/guidance-documents/guidance-on-reach</a></p>