




+ HARNESSING

HEAT SHRINK BOOTS



✓ Active

TE CONNECTIVITY (TE)

202K121-25-01/86-0

Raychem | CAP , CRPS

202K121-25-01/86-0

TE Internal Number: 524735-000

Alias ID: 7-1194121-7

EU RoHS Compliant

EU ELV Compliant

Lipped Yes

Operating Temperature Range (°C) -55 – 105

Fluid/Chemical Resistance Suitable for long term fluid exposure at elevated temperatures

Adhesive Options /86 Precoat, -55 – 105°C (-67 – 221°F)

Material Systems Code 25

↓ **PRODUCT DRAWING**
English

DOCUMENTATION

Product Drawings

Boot, Straight With Lip

PDF

English

FEATURES

Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Molded Part Type Molded Boot

Configuration Features

Lipped Yes

Body Features

Material Systems Code 25

Adhesive Pre-Coat Yes

Entry Size (Braided or Magneform Adapter) 4, 5, 6

Entry Size (Spin Coupling Adapter) 4 – 5

Entry Size (Tinel-Lock Adapter) 4, 5

Material Modified Elastomer

Dimensions

Cable Diameter Range 5.6 – 13 mm [.22 – .512 in]

Wire/Cable Outside Diameter .236 in, .276 in, .3 in, .31 in, .35 in, .39 in, 10 mm, 6 mm, 7 mm, 8 mm, 9 mm

Usage Conditions

Operating Temperature Range (°C) -55 – 105

Operation/Application

Power Cable Accessory No

Industry Standards

Government Qualified No

Approved Standards BS-G-198-5-DE, DEF Std 59-97 Issue 3 Type DE, IEC 62329-3-102, MIS-34867

Other

Fluid/Chemical Resistance Suitable for long term fluid exposure at elevated temperatures

Adhesive Options /86 Precoat, -55 – 105°C (-67 – 221°F)

Adhesive Type High Performance Pre-Coat Adhesive

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
