



+ WIRE AND CABLE

MULTICORE CABLE



✓ Active

TE CONNECTIVITY (TE)

44AM1121-22-9/96-9CS2275

Raychem | RC , SP

44AM1121-22-9/96-9CS2275
TE Internal Number: 718759-000
Mil-Spec: M27500-22ML2T08
Alias ID: 2-1195622-1

EU RoHS Compliant

EU ELV Compliant

Cable Type Spec 44

Number of Strands 19

Strand Size (AWG) 34

Overall Outside Diameter 3.23 mm [.127 in]

Voltage Rating (V) 600

↓ **PRODUCT DRAWING**
English

DOCUMENTATION

Product Drawings

TWO CONDUCTOR CABLE, RADIATION-CROSSLINKED, POLYALKENE-INSULATED, SHIELDED, JACKETED, LIGHTWEIGHT, GENERAL PURPOSE, 600 VOLT

PDF (TIFF AVAILABLE)

English

Product Specifications

Product Specification

Wire And Cable, Electric, Radiation-Crosslinked, Polyalkene-Insulated, Copper Or Copper Alloy

PDF

English

FEATURES

Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Cable Type Spec 44

Shielded Yes

Cable Style Round Braided Shielded & Jacketed

Product Type Cable

Product Classification High Performance - Spec 44, 55 & RCW

Configuration Features

Number of Strands 19

Number of Conductors 2

Electrical Characteristics

Voltage Rating (V) 600

Body Features

Shield Material Tin-Plated Copper

Jacket Color White

Wire Color White with Blue Stripe, White

Conductor Material Tin-Coated Copper

Shield Size (AWG) 38

Dimensions

Strand Size (AWG) 34

Overall Outside Diameter 3.23 mm [.127 in]

Wire Size (AWG) 22

Wire Diameter 1.19 mm [.047 in]

Usage Conditions

Operating Temperature Range (°C) -65 – 150

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
