




**HARNESSING**

**HEAT SHRINK BOOTS**



✓ Active

TE CONNECTIVITY (TE)

**222D285-3/86-0**

Raychem | CAP , CRPS

222D285-3/86-0

TE Internal Number: 353567N001

Alias ID: 4-1192655-5

EU RoHS Compliant

EU ELV Compliant

Lipped Yes

Operating Temperature Range (°C) -55 – 105

Fluid/Chemical Resistance Suitable for occasional exposure to fluids

Adhesive Options /86 Precoat, -55 – 105°C (-67 – 221°F)

Material Systems Code 10

[↓ PRODUCT DRAWING](#)  
English

## DOCUMENTATION

Product Drawings

**Boot, 90 Deg., With Lip**

PDF

English

Product Specifications

Product Specification

**Thermofit Polyolefin Molded Components Flame-Retarded, Semi-Rigid, Heat-Shrinkable**

PDF

English

Product Environmental Compliance

Safety Data Sheet

**Thermofit Heat-Shrinkable Polymeric Products**

PDF

**English**

**Thermofit Heat-Shrinkable Polymeric Products**

PDF

**Danish**

**Thermofit Heat-Shrinkable Polymeric Products**

PDF

**Dutch**

**Thermofit Heat-Shrinkable Polymeric Products**

PDF

**English**

**Thermofit Heat-Shrinkable Polymeric Products**

PDF

**French**

**Thermofit Heat-Shrinkable Polymeric Products**

PDF

**German**

**Thermofit Heat-Shrinkable Polymeric Products**

PDF

**Italian**

**Thermofit Heat-Shrinkable Polymeric Products**

PDF

**Norwegian**

**Thermofit Heat-Shrinkable Polymeric Products**

PDF

**Spanish**

**Thermofit Heat-Shrinkable Polymeric Products**

PDF

**Swedish**

**Thermofit Heat-Shrinkable Polymeric Products**

PDF

**Spanish**

**Thermofit Heat-Shrinkable Polymeric Products**

PDF

**English**

**Aliphatic Polyamide Based Adhesives.**

PDF

**Dutch**

**Aliphatic Polyamide Based Adhesives.**

PDF

**English**

**Aliphatic Polyamide Based Adhesives.**

PDF

**French**

**Aliphatic Polyamide Based Adhesives.**

PDF

**German**

### **Aliphatic Polyamide Based Adhesives.**

PDF

**Italian**

### **Aliphatic Polyamide Based Adhesives.**

PDF

**Spanish**

### **Aliphatic Polyamide Based Adhesives.**

PDF

**Swedish**

### **Thermofit Heat-Shrinkable Polymeric Products**

PDF

**English**

### **Aliphatic Polyamide Based Adhesives.**

PDF

**English**

## **FEATURES**



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

#### Product Type Features

**Molded Part Type** Molded Boot

#### Configuration Features

**Lipped** Yes

#### Body Features

**Material Systems Code** 10

**Adhesive Pre-Coat** Yes

**Entry Size (Braided or Magneform Adapter)** 28

**Entry Size (Solid or Fixed Adapter)** 22 – 24

**Entry Size (Spin Coupling Adapter)** 24 – 28

**Entry Size (Tinel-Lock Adapter)** 28

**Material** Modified Polyolefin

#### Dimensions

**Cable Diameter Range** 17.5 – 39.1 mm [ .689 – 1.539 in ]

**Wire/Cable Outside Diameter** .787 in, .87 in, .9 in, .94 in, 1 in, 1.02 in, 1.1 in, 1.18 in, 1.26 in, 1.34 in, 20 mm, 22 mm, 24 mm, 26 mm, 28 mm, 30 mm, 32 mm, 34 mm

#### Usage Conditions

**Operating Temperature Range (°C)** -55 – 105

Operation/Application

**Power Cable Accessory** No

---

Industry Standards

**Government Qualified** No

**Approved Standards** BS-G-198-5-DA, DEF Std 59-97 Issue 3 Type DA, SAE AS I 81765/1, Type I, UL 224, File E85381

---

Other

**Fluid/Chemical Resistance** Suitable for occasional exposure to fluids

**Adhesive Options** /86 Precoat, -55 – 105°C (-67 – 221°F)

**Adhesive Type** High Performance Pre-Coat Adhesive

---

## PRODUCT COMPLIANCE



Statement of Compliance

**Statement of Compliance**

PDF

---