



HEAT SHRINK TUBING



✓ Active

TE CONNECTIVITY (TE)

X2-4.0-0-SP

Raychem | SWFR X2

EJ1483-000

TE Internal Number: EJ1483-000

EU RoHS Compliant

EU ELV Compliant

Wall Type Single

Resistant To Abrasion

Low Outgassing No

Product Source US

Packaging Method Spool



PRODUCT DRAWING

English

DOCUMENTATION

Product Drawings

SWFR X2 SINGLE WALL HEAT SHRINKABLE TUBING

PDF

English

Catalog Pages/Data Sheets

Highly Flame-Retardant, Zero Halogen, Low Recovery Temperature, Metric-Sized Heat-Shrinkable Tubing

PDF

English

1-1773894-4_SWFR_Tubing

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Wall Type Single

Product Family X2

Electrical Characteristics

Voltage (Max) (kV) .6

Body Features

Shrink Ratio 2:1

Color Black

Flexibility Very Flexible

Material ZEROHAL Polyolefin

Fluid Type Water

Dimensions

Recovered Wall Thickness (Nominal) .46 mm [.018 in]

Expanded Inside Diameter (Min) 4.6 mm [.181 in]

Recovered Inside Diameter (Max) 2 mm [.079 in]

Usage Conditions

Resistant To Abrasion

Recovery Temperature (°C) 90

Operating Temperature Range (°C) -55 – 105

Flammability Flame-Retardant

Shrink Temperature (Min) (°C) 70

Fluid Resistance Moisture/Spray Protection

Product Availability

Applicable Region Global

Packaging Features

Packaging Method Spool

Other

Low Outgassing No

Product Source US

Statement of Compliance

Statement of Compliance

PDF